






7-16 ATTENUATOR 20 DB 4 GHZ 30W

PAGE 1/2 ISSUE 05-09-18C SERIES PART NUMBER R420320110







All dimensions are in mm. Tolerances according ISO 2768 m-H



| COMPONENTS | MATERIALS | PLATING (μm) | |
|-----------------------|------------------|-----------------------------------|--|
| Body | BRASS | BBR 3 | |
| Male center contact | BRASS | GOLD 0.5 OVER NICKEL PHOSPHORUS 2 | |
| Female center contact | BERYLLIUM COPPER | GOLD 0.5 OVER NICKEL PHOSPHORUS 2 | |
| Outer contact | BRASS | BBR 0.5 OVER SILVER 5 | |
| Insulator | PTFE | | |
| Gasket | SILICONE RUBBER | | |
| Substrate | ALUMINA | | |
| Resistor | THICK FILM | | |
| Others parts | ALUMINIUM | BLACK ANODIZATION | |





7-16 ATTENUATOR 20 DB 4 GHZ 30W

| PAGE 2/2 | ISSUE 05-09-18C | SERIES ATTENUATOR | PART NUMBER R420320110 |
|-----------------|------------------------|----------------------|-------------------------------|
|-----------------|------------------------|----------------------|-------------------------------|

ELECTRICAL CHARACTERISTICS

| Frequency (GHz) | DC - 1 | 1 - 2 | 2 - 4 |
|-----------------|--------|-------|-------|
| V.S.W.R (≤) | 1.15 | 1.25 | 1.35 |
| Deviation(±dB) | 0.80 | 0.80 | 0.80 |

| Operating Frequency Range | DC - 4 | GHz |
|------------------------------|--------|-----------------------|
| Impedance | 50 | Ω |
| Nominal Attenuation | 20 | dB |
| Peak power at 25°C (1µs, 1‰) | 5000 | W |
| Average power at 25°C | 25 | W (Free Air Cooled) |
| | | W (Conduction Cooled) |


MECHANICAL CHARACTERISTICS

| Connectors | 7-16 | Male Female | IEC 169-4 |
|------------|----------|-------------|-----------|
| Weight | 439,7900 | g | |

ENVIRONMENTAL CHARACTERISTICS

| Operating temperature range | -40 / +85 | °C | Τ |
|-----------------------------|-----------|----|---|
| Storage temperature range | -40 / +85 | °C | |

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS