





SMA ATTENUATOR 3 DB 6 GHZ 30W

PAGE 1/2 ISSUE 28-05-20A SERIES ATTENUATOR PART NUMBER R422203010





All dimensions are in mm. Tolerances according ISO 2768 m-H



COMPONENTS	MATERIALS	PLATING (μm)	
Body Male center contact	STAINLESS STEEL BERYLLIUM COPPER	PASSIVATED. GOLD 0.5 OVER NICKEL PHOSPHORUS 2	
Female center contact Outer contact	BERYLLIUM COPPER	GOLD 0.5 OVER NICKEL PHOSPHORUS 2	
Insulator	PTFE		
Gasket	SILICONE RUBBER		
Substrate	ALUMINIUM NITRIDE		
Resistor	THICK FILM		
Others parts	ALUMINIUM	BLACK ANODIZATION	





SMA ATTENUATOR 3 DB 6 GHZ 30W

PAGE 2/2	ISSUE 28-05-20A	SERIES ATTENUATOR	PART NUMBER R422203010
-----------------	------------------------	----------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 6
V.S.W.R (≤)	1.25
Deviation(±dB)	0.75

Operating Frequency Range	DC - 6	GHz
Impedance	50	Ω
Nominal Attenuation	3	dB
Peak power at 25°C (1µs, 1‰)	2000	W
Average power at 25°C	30	W (Free Air Cooled)
		W (Conduction Cooled)


MECHANICAL CHARACTERISTICS

Connectors	SMA	Male Female	MIL C39012
Weight	286,21	g	

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55/+125	°C
Storage temperature range	-55/+125	°C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS