





SMA ATTENUATOR 6 DB 2 GHZ 100W

PAGE 1/2 ISSUE 17-08-18B SERIES PART NUMBER R417806138





All dimensions are in mm. Tolerances according ISO 2768 m-H $\,$



COMPONENTS	MATERIALS	PLATING (μm)
Destri	OTAINI FOO OTEF!	DAGGIVATED
Body	STAINLESS STEEL	PASSIVATED
Male center contact	BERYLLIUM COPPER	GOLD 0.5 OVER NICKEL PHOSPHORUS 2
Female center contact	BERYLLIUM COPPER	GOLD 0.5 OVER NICKEL PHOSPHORUS 2
Outer contact		
Insulator	PTFE	
Gasket	SILICONE RUBBER	
Substrate	ALUMINA	
Resistor	THICK FILM	
Others parts	ALUMINIUM	BLACK PAINTING







PAGE 2/2 ISSUE 17-08-18B SERIES PART NUMBER R417806138

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 1	1 - 2
V.S.W.R (≤)	1.10	1.25
Deviation(±dB)	1.0	1.0

Operating Frequency Range	DC - 2	GHz		
Impedance	50	Ω		
Nominal Attenuation	6	dB		
Peak power at 25°C (1µs, 1‰)	5000	W		
Average power at 25°C		W (Free Air Cooled)		
	100	W (Conduction Cooled)		
For conduction cooling, a plate 1000 cm2 x 3 mm(156 sg.in*1/8) min, is required				

For conduction cooling, a plate 1000 cm2 x 3 mm(156 sq.in*1/8) min. is required


MECHANICAL CHARACTERISTICS

Connectors	SMA	Male Female	MIL-C 39012
Weight	468,8800	g	

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55 /+125	°C
Storage temperature range	-55 /+125	°C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS