

Switchmode/High Frequency Common Mode Inductors

ET2424-017

Description:

Common-mode coils are useful in a wide range of applications for the prevention of electromagnetic interference (EMI) and radio frequency interference (RFI) from power supply lines and for prevention of malfunctioning of various electronic equipments. Features include low leakage flux, high self-resonant frequency, high impedance at applicable frequency and low stray capacitance in section winding. Designed to meet UL, CSA and IEC standards.

Electrical Specifications (@20°C):

Min.	Inductance	Max. DC (Ω)	Amps
Inductance*	Difference	Resistance	RMS
(mH)	(µH) Max		
3.20	100	0.20	2.00

^{*}inductance per winding.

Specifications:

Rated Voltage = 250VACTemperature Rise = 45°C Max Insulation Resistance = 100M Ω Min Operating Temperature Range = -20 to 105°C Dielectric Withstanding Voltage = 2,000 VAC


Dimensions:

W	لــ	Ι	Α	В
1.043	1.043	.905	.827	.591

Units in inches.

Weight: .88 oz.

Schematic:




RoHS Compliance: As of manufacturing date February 2016, all standard products meet the requirements of 2015/863/EU, known as the RoHS 3 initiative.


*Upon printing, this document is considered "uncontrolled". Please contact Triad Magnetics website for the most current version. For soldering and washing information please see http://www.triadmagnetics.com/faq.html




460 Harley Knox Blvd. Perris, California 92571









Publish Date: April 18, 2019