
THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO RF INDUSTRIES, ANY UNAUTHORIZED USE OF THIS DRAWING IS EXPRESSLY PROHIBITED WITHOUT WRITTEN PERMISSION FROM RF INDUSTRIES. ANY VIOLATION IS PUNISHABLE UNDER U.S. COPYRIGHT LAWS.

ALL DIMENSIONS ARE REFERENCE ONLY

PAR	RFE-6155					
REV	DESCRIPTION	DWN	DATE	APPROVED		
_	ENGINEERING RELEASE	CZS	04/06/09	JDMc		



SPECIFICATIONS:

IMPEDANCE: 50 Ohms

FREQUENCY RANGE: 0-2 GHz WORKING VOLTAGE: 335 Vrms

INSULATION RESISTANCE: 5k M ohms min. TEMPERATURE RANGE: -65°C TO +85°C

14					000498		Г
13							ı
12							ı
11							ı
10							ı
9							
8	RETAINING RING	1	BRASS	NICKEL, 100μ "			
7	RING	1	DELRIN				⊢
6	WASHER	1	BRASS	NICKEL, 100μ "	DDAWA	1	
5	GASKET	1	SILICONE		DRAWN C. ZUNIGA	04/06/09	
4		1	BRASS	NICKEL, 100μ "	CHECKED	<u> </u>	ı
3	INSULATOR	1	PTFE				ı
2	CONTACT/PIN	1	BRASS	GOLD, 3μ "	ORJ DRAWN	04 /06 /00	ı
1	BODY	1	BRASS	NICKEL, 100μ "	C. ZUNIGA	04/06/09	
#	DESCRIPTION	QTY	MATERIAL	FINISH	APPROVALS	DATE	

DIMENSIONS ARE IN INCHES AND [MILLIMETERS] UNLESS OTHERWISE NOTED TOLERANCES ARE: DECIMALS

DIAMETER



7610 MIRAMAR RD SAN DIEGO, CA 92126 (858) 549-6340 (858) 549-6345 FAX

FME JACK TO TNC PLUG

ADAPTER

SIZE	CABLE GROUP	,	DWG NO.		Т	REV	
Α	N/	Α	RFE-615	55			-
SCALE:	NTS	CAD F	ILE OUTLINE	SHEET	1	OF	1