

APPLICABLE STANDARD							
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO +85 °C <sup>(1)</sup>	STORAGE TEMPERATURE RANGE	-40 °C TO +60 °C <sup>(2)</sup>			
	VOLTAGE	100 V AC	OPERATING HUMIDITY RANGE	85 % MAX <sup>(3)</sup>			
	CURRENT	0.5 A	STORAGE HUMIDITY RANGE	5 % TO 85 % <sup>(2)</sup>			
SPECIFICATIONS							
ITEM	TEST METHOD		REQUIREMENTS			QT	AT
<b>CONSTRUCTION</b>							
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.			x	x
MARKING	CONFIRMED VISUALLY.					x	x
<b>ELECTRIC CHARACTERISTICS</b>							
CONTACT RESISTANCE	100 mA (DC OR 1000 Hz).		40 mΩ MAX.			x	—
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD	20 mV MAX, 1 mA(DC OR 1000Hz)		50 mΩ MAX.			x	—
INSULATION RESISTANCE	250 V DC		100 MΩ MIN.			x	—
VOLTAGE PROOF	300 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.			x	—
<b>MECHANICAL CHARACTERISTICS</b>							
INSERTION AND WITHDRAWAL FORCES	MEASURED BY APPLICABLE CONNECTOR.		INSERTION FORCE : 17.6 N MAX. WITHDRAWAL FORCE : 2.0 N MIN.			x	—
MECHANICAL OPERATION	100 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 50 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.			x	—
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE : 0.75 mm, AT 2 h FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.			x	—
SHOCK	490 m/s <sup>2</sup> , DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.					x	—
<b>ENVIRONMENTAL CHARACTERISTICS</b>							
DAMP HEAT (STEADY STATE)	EXPOSED AT 40±2 °C, 90 ~ 95 %, 96 h.		① CONTACT RESISTANCE: 50 mΩ MAX. ② INSULATION RESISTANCE: 100 MΩ MIN.			x	—
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55→+15~+35→ +85→+15~+35°C TIME 30 → MAX 5 → 30 → MAX 5 min UNDER 5 CYCLES.		③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.			x	—
CORROSION SALT MIST	EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.		① CONTACT RESISTANCE: 50 mΩ MAX. ② NO HEAVY CORROSION.			x	—
HYDROGEN SULPHIDE	EXPOSED IN 3 PPM FOR 96 h. (TEST STANDARD: JEIDA 38)					x	—
RESISTANCE TO SOLDERING HEAT	1) REFLOW SOLDERING : 250 °C MAX, : 220 °C MIN, FOR 60 s 2) SOLDERING IRONS : 360 °C, FOR 5 s		NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.			x	—
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, 240±3°C, FOR IMMERSION DURATION, 3 s.		A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMersed.			x	—
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE		
△							
REMARK <sup>(1)</sup> TEMPERATURE RISE INCLUDED WHEN ENERGIZED. <sup>(2)</sup> THIS STORAGE INDICATES A LONG-TERM STORAGE STATE FOR THE UNUSED PRODUCT BEFORE THE BOARD MOUNTED. <sup>(3)</sup> NON-CONDENSING. Unless otherwise specified, refer to IEC-60512.			APPROVED	HS. OKAWA	15. 07. 17		
			CHECKED	HT. YAMAGUCHI	15. 07. 17		
			DESIGNED	MT. ITANO	15. 07. 17		
			DRAWN	KN. YAMAZAKI	15. 07. 16		
Note	QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELC-084977-92-01			
<b>HRS</b>	SPECIFICATION SHEET		PART NO.	FX6-20S-0. 8SV (92)			
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL576-0101-8-92	△	1/1	