
-			
_	VD	 	 0







LAYOUT SHOWN AS

Keying Shown as example

CHARACTERISTICS

BASIC SERIES:

SHELL SIZE : 19

PLATING : F = Nickel

Н

SHELL TYPE : Square Flange Receptacle

CONTACT TYPE : Standard Crimp Contact

ω

 \sim

-Standard : Based on MIL-DTL-38999 Series III

-Shell Material	: Aluminium
-Shell Plating	: Nickel
-Insulator	: Thermoplastic
-Contacts	: Copper Alloy
-Seals & Grommet	: Silicon Elastomer
-Contact Plating	: Gold over copper Alloy $0.8 \mu m$ minimum
-Durability	: 500 Mating cycles
-Delivered with Souriau contacts and Accessories	
-Temperature Range	: -65°C to +200°C
-Salt Spray	: 48 hours
-Mass	: 30.28 g ± 10%

8D 0

G

19

-

F

32

А

F

Ν

P 3.25±0.2 PP 4.93±0.2 R1 29.36 R2 26.97 S 36.5±0.3
R1 29.36 R2 26.97
R2 26.97
S 36.5±0.3
V 20.83+0/-1.2
W 2.1/2.5
Z 31.5 Max
/V THREAD M28x1-6g


ORIENTATION : N

CONTACT TYPE : PIN(500 Matings)

Е

CONTACT LAYOUT : 19-32

SOURIAU shall	not be liable for
due to a use	of the Products
the Specifications	issued by either
(professi	onal recommend



	Φ		А			
	ľ				4	
	AMPLE				3	
r any non-conformity or damage s which does not comply with er of the Parties or by a third party indation, technical notice.)						
R		Not Listed			2	
9F32AN						
				MOD N°		
		CUSTOME	R DRAWING			
um	Im Receptacle 8D series					
ar	NPRDS / PROJECT 859					
This document is the property of SOURIAU it must not be reproduced or communicated without permission						
	DRG N° 2AN-C			SHEET		
1 34	B		A		J	

