

Customer Part:

Description

- Temperature compensated voltage controlled crystal oscillator (VCTCXO) in a hermetically sealed 3.2x2.5mm SMD package.
- Model IQXT-220-2
- Model Issue number 3

Frequency Parameters

- Frequency 20.0MHz
- Frequency Tolerance ± 1.00 ppm
- Frequency Stability ± 0.28 ppm
- Operating Temperature Range -40.00 to 85.00°C
- Ageing ± 0.02 ppm max/day, ± 1 ppm max/year
- Frequency Tolerance: Measurement referenced to frequency observed with $T_A=25^{\circ}\text{C}$, $V_s=3.3\text{V}$, $V_C=1.5\text{V}$ and load= $10\text{k}\Omega//10\text{pF}$, within 30 days after ex-works.
- Frequency Stability: T_A varied across the operating temperature range, measurement referenced to frequency observed with $f_{\text{ref}}=(f_{\text{max}}+f_{\text{min}})/2$, $V_s=3.3\text{V}$, $V_C=1.5\text{V}$, load= $10\text{k}\Omega//10\text{pF}$ and temperature variable speed less than $2^{\circ}\text{C}/\text{min}$.
- Ageing: V_s , V_C , T_A and load constant, measurement referenced to frequency observed with $T_A=25^{\circ}\text{C}$, $V_s=3.3\text{V}$, $V_C=1.5\text{V}$, load= $10\text{k}\Omega//10\text{pF}$ and after 1hr of operation.
- Supply Voltage Variation (measurement referenced to frequency observed $T_A=25^{\circ}\text{C}$, V_s varied from 3.13V to 3.47V , $V_C=1.5\text{V}$ and load= $10\text{k}\Omega//10\text{pF}$): ± 0.1 ppm max
- Load Variation (measurement referenced to frequency observed with $T_A=25^{\circ}\text{C}$, $V_s=3.3\text{V}$, $V_C=1.5\text{V}$ and load change= $10\text{k}\Omega//10\text{pF} \pm 5\%$): ± 0.1 ppm max

Electrical Parameters

- Supply Voltage $3.3\text{V} \pm 5\%$
- Current Draw 5.000mA
- Current Consumption (@ $T_A=25^{\circ}\text{C}$, $V_s=3.3\text{V}$, $V_C=1.5\text{V}$ and load= $10\text{k}\Omega//10\text{pF}$): 5mA max

Frequency Adjustment


- Pulling ± 10 ppm min to ± 15 ppm max
- Control Voltage $1.5\text{V} \pm 1.0\text{V}$
- Input Impedance $100\text{k}\Omega$ min
- Linearity: 10% max
Slope: Positive

Output Details


- Output Compatibility Clipped Sine
- Drive Capability $10\text{k}\Omega//10\text{pF}$
- Output Voltage Level: 0.8V pk-pk min

Noise Parameters

- Phase Noise @ 25°C ($F=10.0\text{MHz}$, typ):
 - 90dBc/Hz @ 10Hz
 - 120dBc/Hz @ 100Hz
 - 140dBc/Hz @ 1kHz
 - 145dBc/Hz @ 10kHz
 - 148dBc/Hz @ 100kHz

Outline (mm)

Pad Connections

1. Voltage Control
2. GND
3. Output
4. +Vs

Solder Pad Layout

Sales Office Contact Details:

UK: +44 (0)1460 270200

USA: +1.760 668 8935

 Email: info@iqdfrequencyproducts.com

 Web: www.iqdfrequencyproducts.com

Customer Part:**Environmental Parameters**

- Operable Temperature Range: -40 to 85°C
- Storage Temperature Range: -55 to 105°C
- ESD Levels:
 - ESD Human Body Model (JEDEC JS-001-2010): Class 2:
2000V to 4000V
 - ESD Machine Model (JEDEC JESD22-A115C): Class B: 200V
to 400V
- Shock: IEC 60068-2-27, Test Ea, Severity 50A: 100G
acceleration for 6ms, half sine wave, 3 times in 3 mutually
perpendicular planes.
- Vibration: IEC 60068-2-06, Test Fc: 10Hz-2000Hz, 0.75mm
amplitude, 10G acceleration, 30mins per cycle, 3 times in 3
mutually perpendicular planes, test duration 2hrs.

Manufacturing Details

- RoHS Terminations Ni (1µm~9µm), Au (0.5µ~1µm)
- RoHS Reflow Temp 260°C max for 30sec max

Compliance

- RoHS Status (2015/863/EU) Compliant
- REACH Status Compliant
- MSL Rating (JDEC-STD-033): 1

Packaging Details

- Pack Style: Reel Tape & reel in accordance with EIA-481-D
Pack Size: 3,000
- *Alternative packing option available*

Sales Office Contact Details:

UK: +44 (0)1460 270200

USA: +1.760 668 8935

Email: info@iqdfrequencyproducts.comWeb: www.iqdfrequencyproducts.com