



LAYOUT SHOWN AS EXAMPLE

Keying Shown as example

CHARACTERISTICS

- Standard : Based on MIL-DTL-38999 Series III
- Shell Material : Composite
- Shell Plating : Olive drab Cadmium
- Insulator : Thermoplastic
- Contacts : Copper Alloy
- Seals & Grommet : Silicon Elastomer
- Contact Plating : Gold over copper Alloy 0.8µm minimum
- Durability : 500 Mating cycles
- Delivered with Souriau contacts and Accessories
- Temperature Range : -65°C to +175°C
- Salt Spray : 2000 hours
- Mass : 25.9 g ± 10%

| Connector dimension | |
|---------------------|----------|
| Dim | Nominal |
| ØS | 35.7 Max |
| Z' | 31.5 Max |
| VV THREAD | M25x1-6g |

SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)

| Country | Jurisdiction & Control List |
|---------|-----------------------------|
| FR | Not Listed |

PN: 8D517J06AC

| | | | |
|--------------|------------|--------------------------|-------------------------|
| A | 14-10-2016 | First Release | |
| ISS | DATE | Latest modification - by | MOD N° |
| Designed By: | | Date: | CUSTOMER DRAWING |

| | | | |
|--------------|---------------------------------|--|--|
| TITLE | Composite Plug 8D series | | |
|--------------|---------------------------------|--|--|

| | | | |
|-------|--|----------------------------|-----------------|
| SCALE | | General linear Tolerances: | NPRDS / PROJECT |
| NA | | ±-- | 859 |

| | | |
|----------------|------------------------|--|
| SOURIAU | WWW.SOURIAU.COM | This document is the property of SOURIAU it must not be reproduced or communicated without permission |
|----------------|------------------------|--|

| | | |
|-----------|------------------------------------|------------|
| FORMAT | SOURIAU DRG N° 8D517J06AC-C | SHEET |
| A3 | | 1/2 |

| | | | | | | | | | |
|----------------|---------------------------------|---|---|----|---|----|---|---|-----------------|
| BASIC SERIES: | 8D | 5 | - | 17 | J | 06 | A | C | ORIENTATION : C |
| SHELL TYPE : | Plug with RFI Shielding | | | | | | | | |
| CONTACT TYPE : | Standard Crimp Contact | | | | | | | | |
| SHELL SIZE : | 17 | | | | | | | | |
| PLATING : | J = Olive drab Cadmium | | | | | | | | |
| | CONTACT TYPE : PIN(500 Matings) | | | | | | | | |
| | CONTACT LAYOUT : 17-06 | | | | | | | | |

Contact Layout



| Contacts (Insert arrangement 17-6) | | |
|---------------------------------------|-------------|-------------|
| Contact position ID | Location | |
| | X-axis (mm) | Y-axis (mm) |
| A | +121 (3.07) | +209 (5.31) |
| B | +241 (6.12) | +000 (0.00) |
| C | +000 (0.00) | -241 (6.12) |
| D | -241 (6.12) | +000 (0.00) |
| E | -121 (3.07) | +209 (5.31) |
| F | +000 (0.00) | +000 (0.00) |

| Shell size | Arrangement no. | Number of contacts | Size contacts | Service rating | Contact location | Supersedes |
|------------|-----------------|--------------------|---------------|----------------|------------------|------------|
| 17 | -6 | 6 | 12 | I | All | MS20053-6 |

SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)

| Country | Jurisdiction & Control List |
|---------|-----------------------------|
| FR | Not Listed |

PN: 8D517J06AC

| | | | |
|----------------|------------------------------------|----------------------------|---|
| A | 14-10-2016 | First Release | |
| ISS | DATE | Latest modification - by | MOD N° |
| Designed By: | | Date: | CUSTOMER DRAWING |
| TITLE | Composite Plug 8D series | | |
| SCALE | | General linear Tolerances: | NPRDS / PROJECT |
| NA | | ±-- | 859 |
| SOURIAU | WWW.SOURIAU.COM | | This document is the property of SOURIAU it must not be reproduced or communicated without permission |
| FORMAT | SOURIAU DRG N° 8D517J06AC-C | | SHEET 2/2 |