

**Customer Part:**

**Description**

- Ceramic package with a hermetically seam sealed metal lid suitable for automotive applications. Qualified to AEC-Q200 and available with IATF-16949:2016 release. Not suitable for safety critical applications.
- 4 pad
- Model IQXC-180 AUTO-B
- Model Issue number 3

**Frequency Parameters**

- Frequency 12.0MHz
- Frequency Tolerance ±50.00ppm
- Tolerance Condition @25°C ±2°C
- Frequency Stability ±100.00ppm
- Operating Temperature Range -40.00 to 125.00°C
- Overtone Order Fundamental
- Ageing ±5ppm max per year @ 25°C

**Electrical Parameters**

- Load Capacitance (CL) 8.00pF
- Shunt Capacitance (C0) 7pF max
- Drive Level 50µW standard, 200µW max
- ESR 200.00Ω max

**Environmental Parameters**

- Storage Temperature Range: -55°C to +150°C
- Qualified to AEC-Q200

**Manufacturing Details**


- RoHS Terminations NiAu
- RoHS Reflow Temp 260°C max for 10secs max

**Compliance**


- RoHS Status (2015/863/EU) Compliant
- REACH Status Compliant
- MSL Rating (JDEC-STD-033): Not Applicable

**Packaging Details**



- Pack Style: Reel Tape & reel in accordance with EIA-481-D  
Pack Size: 3,000
- *Alternative packing option available*



**Outline (mm)**



- Pad Connections**
1. Crystal
  2. GND
  3. Crystal
  4. GND



**Sales Office Contact Details:**

UK: +44 (0)1460 270200

USA: +1.760 668 8935

Email: [info@iqdfrequencyproducts.com](mailto:info@iqdfrequencyproducts.com)

Web: [www.iqdfrequencyproducts.com](http://www.iqdfrequencyproducts.com)