ت الت الت الت الت الت الت الت الت الت ال	т (Г	U	0	Φ	A	
Z'	ØS					
			LAYOUT SHOWN AS	EXAMPLE		
	Keying Shown as example					
CHARACTERISTICS	Connector dimension	1				
Standard : Based on MIL-DTL-38999 Series III	Dim Nominal					
-Shell Material   : Composite     -Shell Plating   : Nickel     -Insulator   : Thermoplastic     -Contacts   : Copper Alloy	ØS     35.7 Max       Z'     31.5 Max       VV THREAD     M25x1-6g		SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)			
-Seals & Grommet : Silicon Elastomer			Coun	try Jurisdiction & Contr	rol List	
-Contact Plating : Gold over copper Alloy 0.8µm minimum			FR Not Listed			
-Durability : 500 Mating cycles			PN: 8D517M99SAL			
-Delivered without Souriau contacts						
-Temperature Range : -65°C to +200°C -Salt Spray : 2000 hours		A 17-10-2	2016 First Release			
Mass : 26.1 g ± 10%		ISS DATE	E Latest modification - by		MOD N°	
		Designed By:	Date:	CUSTOMER	R DRAWING	
		TITLE	TITLE Composite Plug 8D series			
BASIC SERIES: 8D 5 - 17 N	1 99 S A L	SCALE	General linear Tolerances:	NPRDS /		
SHELL TYPE : Plug with RFI Shielding	Delivered W	/O Contacts NA	±	85		
CONTACT TYPE : Standard Crimp Contact			SOURIAU     This document is the property of SOURIAU       it must not be reproduced or			
	CONTACT TYPE : SOCKET(5		communicated without permission			
SHELL SIZE : 17						
SHELL SIZE : 17 PLATING : M = Nickel	CONTACT LAY	OUT : 17-99 FORMAT A3		J DRG N° I99SAL-C	SHEET	

r	Ŧ	۵	н <b>г</b>	m		0
		Contact Layout				
4	-x	$\begin{array}{c} +Y \\ R & A \\ P \\$				
	B     + 131 (3.3)       C     + 239 (6.07)       D    306 (7.75)       E     + 319 (8.10)       F     + 2.78 (7.06)       G     + 189 (4.80)       H     + 0.67 (1.70)       J     - 0.67 (1.70)       K    189 (4.80)       L    278 (7.26)	Contacts       Contact Iocation       Vraxis (mm)     Contact Iocation       yraxis (mm)     0000     Xaxis (mm)     Yaxis (mm)       231 (8.15)     N     -305 (7.75)     +099 (2.51)       +233 (7.44)     P     -239 (6.07)     +214 (5.44)       x214 (8.15)     N     -305 (7.75)     +099 (2.51)       x200 (2.51)     0.070 (1.70)     +177 (4.50)       x000 (2.51)     0.070 (1.70)     +177 (4.50)       x161 (4.09)     U     +177 (1.50)       x161 (4.09)     U     +175 (4.45)     +094 (2.39)       x260 (6.60)     V     +150 (3.81)     -075 (1.91)       x214 (7.96)     W     +1000 (0.00)     -161 (4.09)       x314 (7.96)     X     -150 (3.81)     -075 (1.91)       x260 (6.60)     Y     -175 (4.45)     +094 (2.39)       -161 (4.09)     Z     +000 (0.00)     +025 (0.64)       -034 (0.86)     X     -150 (3.81)     -075 (1.91)				
ယ	17 00	mber of ntacts     Size contacts     Service rating     Contact position ID     Supersedes       2     16     I     W,Z     MS20053-99       21     20     I     All others     MS20053-99				
	L_				<b></b>	
1	•					SOURIAU shall not be liable for an due to a use of the Products wl the Specifications issued by either o (professional recommenda
N					[	Countr FR
					A 17-10-20	PN: 8D517N
					ISS DATE Designed By:	Latest modification - by Date:
					TITLE	Compo
<u> </u>					SCALE NA	General linear Tolerances: ±
					SOURIA	U WWW.SOURIAU.C
					FORMAT A3	SOURIAU 8D517M
L	Н	G	F	E	D	C

