

SHELL SIZE : 17

PLATING : W = Olive drab Cadmium

G

Н

Е

F

CONTACT TYPE : PIN(500 Matings)

CONTACT LAYOUT : 17-22

FORMAT

Α3

D

due to the Specifica (pr

	4										
LAYOUT SHOWN AS EXAMPLE	3										
JRIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with pecifications issued by either of the Parties or by a third party (professional recommendation, technical notice.) Country Jurisdiction & Control List FR Not Listed PN: 8D717W22AN											
lease MOD N°											
Date: CUSTOMER DRAWING   Aluminium Receptacle 8D series											
General linear   NPRDS / PROJECT     Tolerances:   ±     ±   859     WWW.SOURIAU.COM   This document is the property of SOURIAU it must not be reproduced or	1										
communicated without permissionSOURIAU DRG N°SHEET8D717W22AN-C1/2	_										
C B A	_										

r	т			)		т		т		0	σ		⊳	
			Contact Layout							Panel cutout				
			22						1	JAM NUT RECEPTACLE (TYPE 7)				
4											۸ د			4
			2#12 2#8 Triax											
_	Г		2#0 IIIdX 17-22								<u> </u>			
		Ctc	X	Y						< ØC >				
	-	A B	0 6.32	4.57 0										
		С	0	-4.57					_	Dim     Nominal       B     30.73+0/-0.25	5			
ယ		D	-6.32	0						ØC 32.01+0.25/-0	)			3
	<b> </b> _													
								SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)						
N									CountryJurisdiction & Control ListFRNot Listed					2
									PN: 8D717W22AN					
									A 01-10-2016	First Release				
_									ISS DATE	Latest modification - by			MOD N°	
									Designed By:	Date:		CUSTOMER DRAW	ING	_
									TITLE	Alumi	nium Receptacl	e 8D series		
_ <b>_</b>									SCALE -	General li Tolerand ±		NPRDS / PROJEC <b>859</b>	Т	-
									SOURIAU	WWW.SOURIA	AU.COM	This document is SOUR it must not be re communicated wit	AU eproduced or	
									FORMAT	SOUR	IAU DRG N°		SHEET	_
									A3		7W22AN-C		2/2	
_	Н		(			F		E	D	C	В		Α	