


6	OBSOLETE	△5	101.19 [3.984]	99.06 [3.900]	39	40	9-146304-0		
		△5	98.65 [3.884]	96.52 [3.800]	38	39	8-146304-9		
		△5	96.11 [3.784]	93.98 [3.700]	37	38	8-146304-8		
6	OBSOLETE	△5	93.57 [3.684]	91.44 [3.600]	36	37	8-146304-7		
		△5	91.03 [3.584]	88.90 [3.500]	35	36	8-146304-6		
		△5	88.49 [3.484]	86.36 [3.400]	34	35	8-146304-5		
		△5	85.95 [3.384]	83.82 [3.300]	33	34	8-146304-4		
		△5	83.41 [3.284]	81.28 [3.200]	32	33	8-146304-3		
		△5	80.87 [3.184]	78.74 [3.100]	31	32	8-146304-2		
		△5	78.33 [3.084]	76.20 [3.000]	30	31	8-146304-1		
		△5	75.79 [2.984]	73.66 [2.900]	29	30	8-146304-0		
		△5	73.25 [2.884]	71.12 [2.800]	28	29	7-146304-9		
		△5	70.71 [2.784]	68.58 [2.700]	27	28	7-146304-8		
		△5	68.17 [2.684]	66.04 [2.600]	26	27	7-146304-7		
		△5	65.63 [2.584]	63.5 [2.500]	25	26	7-146304-6		
		△5	63.09 [2.484]	60.96 [2.400]	24	25	7-146304-5		
		△5	60.55 [2.384]	58.42 [2.300]	23	24	7-146304-4		
		6	OBSOLETE	△5	58.01 [2.284]	55.88 [2.200]	22	23	7-146304-3
△5	55.47 [2.184]			53.34 [2.100]	21	22	7-146304-2		
△5	52.93 [2.084]			50.80 [2.000]	20	21	7-146304-1		
△5	50.39 [1.984]			48.26 [1.900]	19	20	7-146304-0		
△5	47.85 [1.884]			45.72 [1.800]	18	19	6-146304-9		
△5	45.31 [1.784]			43.18 [1.700]	17	18	6-146304-8		
△5	42.77 [1.684]			40.64 [1.600]	16	17	6-146304-7		
△5	40.23 [1.584]			38.10 [1.500]	15	16	6-146304-6		
△5	37.69 [1.484]			35.56 [1.400]	14	15	6-146304-5		
△5	35.15 [1.384]			33.02 [1.300]	13	14	6-146304-4		
△5	32.61 [1.284]			30.48 [1.200]	12	13	6-146304-3		
△5	30.07 [1.184]			27.94 [1.100]	11	12	6-146304-2		
△5	27.53 [1.084]			25.40 [1.000]	10	11	6-146304-1		
6	OBSOLETE			△5	24.99 [.984]	22.86 [.900]	9	10	6-146304-0
				△5	22.45 [.884]	20.32 [.800]	8	9	5-146304-9
6	OBSOLETE	△5	19.91 [.784]	17.78 [.700]	7	8	5-146304-8		
		△5	17.37 [.684]	15.24 [.600]	6	7	5-146304-7		
6	OBSOLETE	△5	14.83 [.584]	12.70 [.500]	5	6	5-146304-6		
		△5	12.29 [.484]	10.16 [.400]	4	5	5-146304-5		
6	OBSOLETE	△5	9.75 [.384]	7.62 [.300]	3	4	5-146304-4		
		△5	7.21 [.284]	5.08 [.200]	2	3	5-146304-3		
6	OBSOLETE	△5	4.67 [.184]	2.54 [.100]	1	2	5-146304-2		
		△5	2.13 [.084]	-	0	1	5-146304-1		
PLATING		C	B	A	NO OF POSITIONS	PART NUMBER			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN I. HOFFMAN 21JUN95	 TE Connectivity
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
0 PLC ± -	1 PLC ± -	2 PLC ± 0.51[.020]	NAME
3 PLC ± 0.12[.005]	4 PLC ± 0.012[.0005]	ANGLES ± -	PRODUCT SPEC
MATERIAL △4	FINISH SEE TABLE	WEIGHT -	APPLICATION SPEC
CUSTOMER DRAWING		SCALE 1:1	RESTRICTED TO

SIZE A1 CAGE CODE DRAWING NO 00779 C=146304

HEATER ASSEMBLY, MOD II, BREAKAWAY, HIGH TEMPERATURE, RIGHT ANGLE, SINGLE ROW, .100 C/L, W/.025 SQUARE POSTS

SHEET 2 OF 2 REV C