



SIGN	DATE	DESCRIPTION	APPROVER
△	01/25'05	Part No. changed.	Marvin
△	06/26'06	Current rating(cULus) is changed from 10A to 20A	Marvin
△	06/26'06	Solid/Stranded wire(AWG) is changed from 12-22 to 12-24	Marvin
△	8/10'06	Added VDE and TUV standard	梁仁松
△	7/21'08	Body is changed.	Marvin
△	2010.03.08	Add the 2P mark	Jacke
△	2014.11.14	Update the drawing	Evan

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item ① Clamp: Brass(CuZn) Ni plated
- Item ② Terminal screw: Steel Zinc plating "-" slot type
- Item ③ Female contact: PhBz ,Tin plated
- Item ④ Terminal Cover: Thermoplastic (UL94V-0)
- Item ⑤ Terminal housing: Thermoplastic (UL94V-0)
- △ Electrical cULus/VDE/TUV
 - Voltage rating: 300VAC/300VAC/300VAC
 - Current rating: 20A/20A/20A
 - Wire range: 2.5mm²/0.34-2.5mm²
 - Solid wire(AWG): 12-24
 - Stranded wire(AWG): 12-24
 - Torque: 5Lb-In/0.5Nm/0.56Nm
 - Screw: M3
 - Wire strip length: 7-8mm
 - Withstanding Voltage: 1.6KV/2.5KV/2.5KV
 - Operating temperature: -40°C to +115°C
 - Safety Approval: cULus VDE TUV
 - Use with 0Q1.0x1.0mm square pin, Withdrawal force:200 - 500gf /pole
 - Critical dimension: ▽

TJ xx 51 x 3 xxxx G △

- 02 2 CONTACTS
- 03 3 CONTACTS
-
- 24 24 CONTACTS

- 0 Black (RAL9005)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)
- 9 White(RAL1102)
- C Green(RAL6018/U)

RoHS compliant
(lead<4%)
In copper Alloy

000 0 Standard @ Logo
000 A Standard ANY Logo
0091 Standard ANY Logo △
Any special item by
customer request,
please contact sales
department.

DIMENSION

L	N×5.08
A	(N-1)×5.08
B	N×5.08+0.1

N=Number of poles

Poles	Tolerance	
	DIM A	DIM L&DIM B
2p-6p	±0.15	±0.20
7p-12p	±0.20	±0.25
13p-18p	±0.25	±0.30
19p-24p	±0.30	±0.40

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		TJ-5.08mm Series 2P-24P			
PART NO.		TJxx51x3xxxxG		DWG NO. 8TJ0007	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Evan 2014.11.14	Evan 2014.11.14		
				UNIT: mm SCALE: NONE SHEET: 01/01 REV.: H	
				Tolerance X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°	