



DIMENSION

Dim A	(N-1) × 5.08+7.08
Dim B	(N-1) × 5.08
Dim C	(N-1) × 5.08+5.48

N = Number of poles

Poles	Tolerance (Dim A&B&C)
2p-6p	±0.15
7p-12p	±0.25
13p-16p	±0.35
17p-24p	±0.40

REV	SIGN	DATE	DESCRIPTION	APPROVER
B		10/23-18	Initial release	zhangcan
<i>THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!</i>				

- Material:**
- Item Ⓐ Contact pin: Copper Bright Tin plated over Nickel plated
 - Item Ⓑ Insulator(housing): Thermoplastic (UL94V-0)

- Electrical:** cULus
- Voltage rating: 300V
 - Current rating: 20A
 - Withstanding Voltage: 16 KV
 - Operating temperature: -40°C to +115°C
 - Wave soldering temperature: 260°C±5°C/5 Sec
 - Safety Approval: cULus
 - Critical dimension:

00 XX 5 4 X A XXXX G

No. OF POLES: 02: 2 POLES, 24: 24 POLES

RoHS compliant (lead<4%) In copper Alloy

0000 "Ⓐ" Logo
000A "ANY" Logo

COLOR

0	Black (RAL9005)	...
2	Red (RAL3001/D)	...
3	Orange(RAL2011/P)	Any special item by customer request, please contact sales department
4	Yellow(RAL1018/A)	
5	Green(RAL6018/T)	
6	Blue (RAL5015/A)	
8	Grey(RAL7035/D)	
9	White(RAL1102)	
C	Green(RAL6018/U)	

Amphenol

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD.

TITLE	00 5.08mm 90° Close Series 2p-24p 任何特		DWG NO.	80007161	Tolerance
PART NO.	00xxx54xxxxxxG	CUST. NO.			X ±0.50
CHECKED	zhangcan	DRAWN	zhangcan		X.X ±0.30
DESIGNED	10/23-18				X.XX ±0.10
APPROVED					X° ±1°

SHEET: 01/01 REV.: B