



- ✓ 12 Watts Output Power
- ☑ 3.3 VDC to 48 VDC Single Outputs
- ☑ Universal 90-264 VAC Input, 50/60/440 Hz
- ☑ 3,000 VAC Input to Output Isolation
- ✓ EN55022 Class B EMI
- ☑ IEC 62368-1 and IEC 60950-1 Safety



### **PRODUCT MODELS**

Model	Output Voltage	Output Current	Output Power	Size (inches)	Typical Efficiency
SIP Style Open Frame					
PWC12-3.3S	3.3 VDC	3.01 A	10 W	1.12 x 2.0 x 0.83	72%
PWC12-5S	5 VDC	2.4 A	12 W	1.12 x 2.0 x 0.83	75%
PWC12-9S	9 VDC	1.34 A	12 W	1.12 x 2.0 x 0.83	78%
PWC12-12S	12 VDC	1.0 A	12 W	1.12 x 2.0 x 0.83	80%
PWC12-15S	15 VDC	0.8 A	12 W	1.12 x 2.0 x 0.83	80%
PWC12-24S	24 VDC	0.5 A	12 W	1.12 x 2.0 x 0.83	82%
PWC12-48S	48 VDC	0.25 A	12 W	1.12 x 2.0 x 0.83	82%
SIP Style Encapsulated	d				
PWC12-3.3SE	3.3 VDC	3.01 A	10 W	1.24 x 2.11 x 0.92	72%
PWC12-5SE	5 VDC	2.4 A	12 W	1.24x 2.11 x 0.92	75%
PWC12-9SE	9 VDC	1.34 A	12 W	1.24 x 2.11 x 0.92	78%
PWC12-12SE	12 VDC	1.0 A	12 W	1.24 x 2.11 x 0.92	80%
PWC12-15SE	15 VDC	0.8 A	12 W	1.24 x 2.11 x 0.92	80%
PWC12-24SE	24 VDC	0.5 A	12 W	1.24 x 2.11 x 0.92	82%
PWC12-48SE	48 VDC	0.25 A	12 W	1.24 x 2.11 x 0.92	82%



# **Power Block Micro-Miniature 12 Watt Switching Power Supplies**

Model	Output Voltage	Output Current	Output Power	Size (inches)	Typical Efficiency
DIP Style Open Fram	ne				
PWC12-3.3	3.3 VDC	3.01 A	10 W	1.0 x 2.0 x 0.9	72%
PWC12-5	5 VDC	2.4 A	12 W	1.0 x 2.0 x 0.9	75%
PWC12-9	9 VDC	1.34 A	12 W	1.0 x 2.0 x 0.9	78%
PWC12-12	12 VDC	1.0 A	12 W	1.0 x 2.0 x 0.9	80%
PWC12-15	15 VDC	0.8 A	12 W	1.0 x 2.0 x 0.9	80%
PWC12-24	24 VDC	0.5 A	12 W	1.0 x 2.0 x 0.9	82%
PWC12-48	48 VDC	0.25 A	12 W	1.0 x 2.0 x 0.9	82%
DIP Style Encapsulat	ted				
PWC12-3.3E	3.3 VDC	3.01 A	10 W	1.07 x 2.06 x 0.91	72%
PWC12-5E	5 VDC	2.4 A	12 W	1.07 x 2.06 x 0.91	75%
PWC12-9E	9 VDC	1.34 A	12 W	1.07 x 2.06 x 0.91	78%
PWC12-12E	12 VDC	1.0 A	12 W	1.07 x 2.06 x 0.91	80%
PWC12-15E	15 VDC	0.8 A	12 W	1.07 x 2.06 x 0.91	80%
PWC12-24E	24 VDC	0.5 A	12 W	1.07 x 2.06 x 0.91	82%
PWC12-48E	48 VDC	0.25 A	12 W	1.07 x 2.06 x 0.91	82%



# **Power Block Micro-Miniature 12 Watt Switching Power Supplies**

#### INPUT SPECIFICATIONS

Input Voltage Range	90-264VAC		
Input Frequency	47-440 Hz (50-60 Hz nom.)		
Inrush Current	20A typ at 115VAC		
	40A typ at 230VAC		

### MAIN OUTPUT SPECIFICATIONS

Output Voltage	See model selection table
Output Power	See model selection table
Preset Accuracy (Note 8)	±1.5% typ, Vout = 3.3V
	±1% typ, Vout = 5~48V
Load Regulation (Note 6)	±1% max
Line Regulation (Note 7)	±0.5% max
Efficiency	See model selection table
Temperature Coefficient	±0.03%/°C (0~50°C, typ.)
Ripple/Noise (20MHz BW)	150mV pk-pk max
	(Notes 1, 2 &9)
Hold-up Time, full load	16ms typ
Over Voltage Protection*	Clamp
Short Circuit Protection*	Latching, Recovering
Over Temp Protection *	Latching, Recovering

### **GENERAL SPECIFICATIONS**

Input to Output Isolation	3000VAC (Note 3)
Switching Frequency	132 kHz fixed, typ

### **MECHANICAL SPECIFICATIONS**

Size	See model selection table
Package Types	Open Frame, Encapsulated

#### SAFETY AND COMPLIANCE CERTIFICATIONS


Safety Approvals	IEC 62368-1 and IEC 60950-1,		
	cURus, UL-EU, CSA C22.2, CB, CE		
Conducted and	EN 55022 (CISPR22), Class B		
Radiated Emissions			

All Specifications are typical at nominal input, full load, 25°C unless specified otherwise.

#### **ENVIRONMENTAL SPECIFICATIONS**

Operating Temperature	-20 to +50°C at Full Load,
(Note 4)	up to +70°C with Derating*
	See derating chart
Cooling	Free Air Convection
Storage Temperature*	-40 to +85°C
Operating Humidity	0% to 95%, non-condensing
MTBF (MIL-HDBK-217F)	466,553 hrs

#### THERMAL DERATING



#### Notes:


- 1. All measurements should be made directly at the terminals of the power supply
- 2. Ripple and noise dependent upon output voltage as specified per particular model.
- 3. Isolation for up to 1 minute duration.
- 4. Specified for free air convection cooling.
- 5. Minimum load is not required for proper operation.
- 6. Load Regulation is measured from 5% to Full Load.
- 7. Line Regulation measured from High Line to Low Line.
- 8. Preset Accuracy measured at nominal load, 120VAC input.
- 9. O/P Noise measured directly at the pins/ terminals at nominal load, 0.1uF bypass and 47uF electrolytic, pk-pk @ 20MHz bandwidth.
- 10. 100% Production Tested


<sup>\*</sup> These are stress ratings. Exposure of the devices to any of these conditions may adversely affect long term reliability. Operation under conditions other than the standard operating conditions is neither warrantied nor implied.

# **Power Block Micro-Miniature 12 Watt Switching Power Supplies**


### **OUTLINE DRAWINGS**


# **SIP Style Open Frame**






## **SIP Style Encapsulated**







# **DIP Style Open Frame**



# **DIP Style Encapsulated**

