

Wireless Charging Receiver Module

Scope

- This document is consistent with WPC and PMA standard receiver modules described.
- The Wireless Power supply's Rx Module shall meet the ROHS requirement.

Applications

- Smartphone, Notebooks, Tablets
- Wearable devices
- Game accessories
- Power bank, Charging case
- Computer peripheral devices
- Medical Care

Product Characteristic

The QPR-0303 device is a fully contained wireless power receiver capable of operating in both WPC and PMA protocols which allows a wireless power system to work with both WPC and PMA inductive charging standards. The QPR-0303 device provides a single device power conversion (rectification and regulation) as well as the digital control and communication for both standards. It also has autonomous detection of protocol and requires no additional active devices. The QPR-0303 device complies with the WPC1.2.2 Qi and PMA communication protocol. Together with the WPC or a PMA primary-side controller, the Ti BQ51222 device enables a complete wireless power transfer system for a wireless power supply solution. The receiver allows for synchronous rectification, regulation and control and communication to all exist in a market-leading form factor, efficiency, and solution size.

Input Characteristics

Input Voltage & Frequency

Item	Minimum	Normal	Maximum
Input Frequency	110kHz	145kHz	205kHz
Input Voltage	6.5VAC	7.5VAC	15.5VAC

Energy Consumption
At 7.5VAC or 15.5VAC, Energy Consumption ≤ 0.01A.

Output Characteristics (Rx Module)

Static Output Characteristics (Vo & R+N)

Output Voltage	Rated Load		Peak	Output Range	R + N
Output voitage	Min. Load	Load Max. Load	Peak	Output Kange	N T IN
5V DC	0.05A	1A	1.2A	5V ± 5.0%	\leq 250m Vp-p

Note

Ripple & Noise: Measurement is done by 20MHz bandwidth oscilloscope and the output end paralleled a 0.1uF ceramic capacitor and a 10uF electrolysis capacitor.

Line & Load Regulation

Output Voltage	Load Condition		Line Regulation	Load Bogulation
Output Voltage	Min. Load	Max. Load	Line Regulation	Load Regulation
5V DC	0.05A	1A	± 5.0%	± 5.0%



Wireless Charging Receiver Module

Protection Requirement

Short Circuit Protection

The input power shall decrease when the output is short to GND, the power supply shall not damage, and shall be self-recovery when the fault condition is removed.

Over Current Protection

OCP Point Limited: 120%~130% auto restart.

The output shall hiccup when the over current applied to the output, and shall be self-recovery when the fault condition is removed.

Reliability Requirements

Reliability Test

Test Items	Test Conditions	
Storage at high temperature test	+60°C, 16hours	
Storage at low temperature test	-20°C, 16hours	
Operating at high temperature test	+40°C, 8hours	
Operating at low temperature test	-20°C, 8hours	
High/Low temperature cycle test	+45°C (2Hrs) → -20°C (2Hrs) → +45°C (2Hrs) → -20°C (2Hrs) continually work 24hours	

• Burn-in: 2hours under 35°C (±5°C), nominal input voltage, nominal load.

Environment Requirement

- Operating Temperature and Relative Humidity 0°C to +40°C, 20%RH to 80%RH @ altitude should be below 10000 feet.
- Storage Temperature and Relative Humidity -20°C to +60°C, 10%RH to 90%RH (non-condensing) @ altitude should be below 30000 feet.


Execution Standards (Compatible with these specifications)

EMC Standards

GB9254	GB17625.1	GB13837	FCC-Part15
EN55022	EN55024	CISPR22	EN61000-4-4
EN61000-3-2	EN61000-3-3	EN61000-4-2	EN61000-4-3
EN61000-4-5	EN61000-4-6	EN61000-4-8	EN61000-4-11

WPC V1.2.2 Qi Standards

Photo of Product






Wireless Charging Receiver Module

Module

Product Design Proposal

According to the standardization of QI, there is three principles need to be careful:

- (1) The distance between Tx Coil with PCB and other metal components is Min: 5.0mm
- (2) The distance between the surface of Tx Coil and the surface of product (Working Face) is $2.0_{-0.25}^{+0.5}$ mm, which means the thickness of the working face plastic is not more than 2.5mm.
- (3) The surface distance between Tx Coil and Rx Coil is 3.5~4.5mm.
- PCBA Port Functional Illustration




(Unit: mm)

PCBA: 30 * 18 * 1.6 mm (Max.)

Coil + Shielding: 48 * 35 * 1.5 mm (Max.)

Amount of space between the PCBA to Coil+Shielding as follows: 15 ± 2 mm





Pin Description

Port	CI	N1	CN3	
	Right Pin	Left Pin	Left Pin	Right Pin
Function	OUT+	GND	OUT+	GND
Dort		1	CN4	
Port	L		Ö	N -1
Port	Left Pin	Right Pin	Up Pin	Down Pin

Wireless Charging Receiver Module

Rx Coil Spec





Others

■ Weight: 6 ± 1 g

Major Test Equipment

- (1) DC Supply
- (2) Qi Tx_Module
- (3) Electronic Load
- (4) DPO3014 Digital Phosphor Oscilloscope
- (5) Logical Analyzer
- (6) AVID Technologies Qi Sniffer