





4.3-10 FEMALE TERMINATION 6 GHZ 30W

PAGE 1/2	ISSUE 07-11-19B	SERIES TERMINATION	PART NUMBER <b>R404759000</b>
----------	-----------------	-----------------------	-------------------------------





All dimensions are in mm. Tolerances according ISO 2768 m-H



COMPONENTS	MATERIALS	PLATING (μm)
Body	BRASS	NICKEL 2
Center contact	BERYLLIUM COPPER	GOLD 0.5 OVER NICKEL 2
Outer contact	BERYLLIUM COPPER	SILVER 5
Insulator	PTFE	
Gasket		
Substrate	ALUMINIUM NITRIDE	
Resistor	THICK FILM	
Others parts	ALUMINIUM	BLACK ANODIZATION





4.3-10 FEMALE TERMINATION 6 GHZ 30W

PAGE <b>2/2</b>	ISSUE 07-11-19B	SERIES TERMINATION	PART NUMBER <b>R404759000</b>
-----------------	-----------------	-----------------------	-------------------------------

# **ELECTRICAL CHARACTERISTICS**

Frequency (GHz)	DC - 3	3 - 6
V.S.W.R (≤)	1.20	1.40

DC - 6	GHz
50	Ω
50	Ω ± 5%
2000	W
30	W (Free Air Cooled)
	W (Conduction Cooled)
	50 50 2000


# **MECHANICAL CHARACTERISTICS**

Connectors	4.3-10	Female	IEC 60169-54
Weight	<b>220,5500</b> g		

### **ENVIRONMENTAL CHARACTERISTICS**

Operating temperature range	-55/+125	°C
Storage temperature range	-55/+125	°C

#### Power derating Versus temperature



## SPECIFICATION

## **OTHER CHARACTERISTICS**

# MOUNTED WITH VERTICAL COOLING FINS AND NATURAL CONVECTION