

Features

- Halogen Free. "Green" Device (Note 1)
- · AEC-Q101 Qualified
- · For Switching and AF Amplifier Applications
- · Moisture Sensitivity Level 1
- Epoxy Meets UL 94 V-0 Flammability Rating
- Lead Free Finish/RoHS Compliant ("P" Suffix Designates RoHS Compliant. See Ordering Information)

Maximum Ratings

- Operating Junction Temperature Range: -55°C to +150°C
- Storage Temperature Range: -55°C to +150°C
- Thermal Resistance: 320°C/W Junction to Solder-point (Note2)
- Thermal Resistance: 403°C/W Junction to Ambient (Note2)

Parameter	Symbol	Rating	Unit
Collector-Base Voltage	V _{CBO}	-80	V
Collector-Emitter Voltage	V _{CEO}	-65	V
Emitter-Base Voltage	V _{EBO}	-5	V
Collector Current	I _C	-100	mA
Peak Collector Current	I _{CM}	-200	mA
Peak Emitter Current	I _{EM}	-200	mA
Power Dissipation (Note2)	P _D	310	mW

Note: 1. Halogen free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.


Package Mounted 1.0*1.0mm Pad Layout 1oz Copper That is On a Single-sided FR4 PCB.

Part Number	BC856AHE3	BC856BHE3		
Marking	3A	3B		

Internal Structure




PNP Small Signal Transistor



DIMENSIONS						
DIM INCHES		HES	M	М	NOTE	
Dilvi	MIN		MIN	MAX	NOTE	
Α	0.110	0.120	2.80	3.04		
В	0.083	0.104	2.10	2.64		
С	0.047	0.055	1.20	1.40		
D	0.034	0.041	0.85	1.05		
E	0.067	0.083	1.70	2.10		
F	0.018	0.024	0.45	0.60		
G	0.0004	0.006	0.01	0.15		
Н	0.035	0.043	0.90	1.10		
J	0.003	0.007	0.08	0.18		
K	0.014	0.020	0.35	0.51		
L	0.007	0.020	0.20	0.50		

Suggested Solder Pad Layout






Electrical Characteristics @ 25°C Unless Otherwise Specified


Parameter		Symbol	Min	Тур	Max	Units	Conditions
Collector-Base Breakdown Voltage	ge ^(Note3)	$V_{(BR)CBO}$	-80			V	I_{C} =-10 μ A, I_{E} =0
Collector-Emitter Breakdown Volt	tage ^(Note3)	$V_{(BR)CEO}$	-65			V	I _C =-10mA, I _B =0
Emitter-Base Breakdown Voltage	(Note3)	$V_{(BR)EBO}$	-5			>	I_{E} =-1 μ A, I_{C} =0
Collector-Cutoff Current (Note3)					-15	nA	V _{CB} =-30V
Collector-Cutoff Current (*****)		I _{CBO}			-4	μA	V _{CB} =-30V, T _A =150°C
DC Current Gain ^(Note3)	BC856AHE3	h	125	180	250		V_{CF} =-5Vdc, I_{C} =-2mA
DC Current Gain	BC856BHE3	h _{FE}	220	290	475		VCESVGC, ICZIIIA
Small Signal Current Gain	BC856AHE3	h _{fe}		200			
Sitiali Signal Current Gain	BC856BHE3	' Ife		330			
Input Impedance	BC856AHE3	h _{ie}		2.7		ΚΩ	\\ _ F\\
Imput impedance	BC856BHE3	' 'ie		4.5		1/(2)	V _{CE} =-5V I _C =-2mA
Output Admittance	BC856AHE3	h _{oe}		18		μS	f=1KHz
	BC856BHE3			30			
Reverse Voltage Transfer Ratio	BC856AHE3	- h		1.5x10 ⁻⁴			
Reverse voltage Transfer Natio	BC856BHE3			2x10 ⁻⁴			
O-II4 (Note3)		V _{CE(sat)}		-75	-300	mV	I _C =-10mA, I _B =-0.5mA
Collector-Emitter Saturation Volta	Collector-Emitter Saturation Voltage ^(Note3)			-250	-650	mV	I_C =-100mA, I_B =-5mA
Dana Fusithan Catamatian Valtana	Note3)	V _{BE(sat)}		-700		mV	I _C =-10mA, I _B =-0.5mA
Base-Emitter Saturation Voltage	Base-Emitter Saturation Voltage ^(Note3)			-850		mV	I_C =-100mA, I_B =-5mA
Base-Emitter Voltage (Note3)		V _{BE}	-600	-650	-750	mV	V_{CE} =-5V, I_{C} =-2mA
					-820	mV	V _{CE} =-5V, I _C =-10mA
Current Gain-Bandwidth Product		f _T	100	200		MHz	V_{CE} =-5V, I_{C} =-10mA, f=100MHz
Collector-Base Capacitance		C _{CBO}		3		pF	V _{CB} =-10V, f=1MHz
Noise Figure		NF		0	10	10 dB	V _{CE} =-5V, I _C =-200μA
				2	10		R_S =2KΩ, f=1KHz, Δ f=200Hz


Note: 3. Short Duration Pulse Test to Minimize Self-heating Effect.





Curve Characteristics
















Ordering Information

Device	Packing			
Part Number-TP	Tape&Reel: 3Kpcs/Reel			

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp**. does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp**, and all the companies whose products are represented on our website, harmless against all damages. **Micro Commercial Components Corp**, products are sold subject to the general terms and conditions of commercial sale, as published at

https://www.mccsemi.com/Home/TermsAndConditions.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

Rev.3-4-06122022 4/4 MCCSEMI.COM