






N ATTENUATOR 6 DB 2 GHZ 80/100W

PAGE 1/2 ISSUE 12-04-16B SERIES ATTENUATOR PART NUMBER R417706128

# **SCALE 1:2**







All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
5 1	074111 F00 07FF1	DAGGNATED
Body	STAINLESS STEEL	PASSIVATED
Male center contact	BERYLLIUM COPPER	GOLD 0.5 OVER NICKEL PHOSPHORUS 2
Female center contact	BERYLLIUM COPPER	GOLD 0.5 OVER NICKEL PHOSPHORUS 2
Outer contact	-	-
Insulator	PTFE	
Gasket	SILICONE RUBBER	
Substrate	ALUMINA	
Resistor	THICK FILM	
Others parts	ALUMINIUM	BLACK PAINTING





N ATTENUATOR 6 DB 2 GHZ 80/100W

PAGE <b>2/2</b>	ISSUE <b>12-04-16B</b>	SERIES ATTENUATOR	PART NUMBER <b>R417706128</b>
-----------------	------------------------	----------------------	-------------------------------

### **ELECTRICAL CHARACTERISTICS**

Frequency (GHz)	DC - 1	1 - 2
V.S.W.R (≤)	1.10	1.25
Deviation(±dB)	1	1

Operating Frequency Range	DC - 2	GHz
Impedance	50	Ω
Nominal Attenuation	6	dB
Peak power at 25°C (1µs, 1‰)	5000	W
Average power at 25°C	80	W (Free Air Cooled)
	100	W (Conduction Cooled)


#### MECHANICAL CHARACTERISTICS

Connectors	N	Male Female	MIL-C 39012
Weight	<b>618,0200</b> g		

### **ENVIRONMENTAL CHARACTERISTICS**

Operating temperature range	-55 /+125	°C
Storage temperature range	-55 /+125	°C

#### Power derating Versus temperature



## SPECIFICATION

# OTHER CHARACTERISTICS