





TNC ATTENUATOR 3 DB 2 GHZ 80/100W

PAGE 1/2	ISSUE 17-08-18B	SERIES ATTENUATOR	PART NUMBER R417903128
-----------------	------------------------	----------------------	-------------------------------





All dimensions are in mm. Tolerances according ISO 2768 m-H $\,$



COMPONENTS	MATERIALS	PLATING (μm)	
Body Male center contact	STAINLESS STEEL BERYLLIUM COPPER	PASSIVATED GOLD 0.5 OVER NICKEL PHOSPHORUS 2	
Female center contact Outer contact	BERYLLIUM COPPER	GOLD 0.5 OVER NICKEL PHOSPHORUS 2	
Insulator	PTFE		
Gasket	SILICONE RUBBER		
Substrate	ALUMINA		
Resistor	THICK FILM		
Others parts	ALUMINIUM	BLACK PAINTING	



Technical Data Sheet

TNC ATTENUATOR 3 DB 2 GHZ 80/100W

PAGE 2 / 2	ISSUE 17-08-18B	SERIES ATTENUATOR	PART NUMBER R417903128
PAGE 2 / 2	ISSUE 17-08-18B	SERIES ATTENUATOR	PART NUMBER R417903128

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 1	1 - 2
V.S.W.R (≤)	1.10	1.25
Deviation(±dB)	1.0	1.0

Operating Frequency Range	DC - 2	GHz
Impedance	50	Ω
Nominal Attenuation 3		dB
Peak power at 25°C (1µs, 1‰)	5000	W
Average power at 25°C	80	W (Free Air Cooled)
	100	W (Conduction Cooled)
For conduction cooling, a plate 1000 cm2 x 3 mm/156 sg.in*1/8) min, is required		


MECHANICAL CHARACTERISTICS

Connectors	TNC	Male Female	MIL-C 39012
Weight	603,9500	g	

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55 /+125 °C
Storage temperature range	-55 /+125 °C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS