

Page 1 of 3

## RH100-40.000-15-F-3030-EXT-TR


## SPECIFICATIONS

PARAMETER	VALUE
NOMINAL FREQUENCY	40.000 MHz
MODE OF OSCILLATION	Fundamental
FREQUENCY TOLERANCE AT 25°C	±30 ppm max
FREQUENCY STABILITY OVER TEMPERATURE	±30 ppm max
OPERATING TEMPERATURE RANGE	-40°C to +85°C
STORAGE TEMPERATURE RANGE	-40°C to +85°C
AGING	±2 ppm first year max
LOAD CAPACITANCE	15 pF
EQUIVALENT SERIES RESISTANCE	50 $\Omega$ max
SHUNT CAPACITANCE	3.5 pF max
DRIVE LEVEL	200 µW max
REFLOW CONDITIONS	260°C for 10 sec max




Photo is not actual part

## MECHANICAL SPECIFICATION



# **CARRIER TAPE DIMENSIONS**



NOTE: REFER TO EIA-481 FOR DIMENSIONS

### PACKAGING

178 mm REEL DIAMETER 8 mm TAPE WIDTH, 4 mm PITCH QUANTITY: 3000 PIECES PER REEL


IN ACCORDANCE WITH EIA-481



Page 2 of 3

### RH100-40.000-15-F-3030-EXT-TR

## • REFLOW PROFILE



Reflow profile				
Temperature Min Preheat	T <sub>SMIN</sub>	150°C		
Temperature Max Preheat	T <sub>SMAX</sub>	200°C		
Time (T <sub>SMIN</sub> to T <sub>SMAX</sub> )	ts	60-180 sec.		
Temperature	TL	217°C		
Peak Temperature	T <sub>P</sub>	260°C		
Ramp-up rate	Rup	3°C/sec max.		
Ramp-down rate	RDOWN	6°C/sec max.		
Time within 5°C of Peak Temperature	tP	10 sec.		
Time t[25°C] to Peak Temperature	t[25°C] to Peak	480 sec.		
Time	t∟	60-150 sec.		

## ENVIRONMENTAL

PARAMETER	VALUE
MOISTURE SENSITIVITY LEVEL	1
RoHS	Compliant
REACH SVHC	Compliant
HALOGEN-FREE	Compliant
ESD CLASSIFICATION LEVEL	N/A
TERMINATION FINISH	Au





Page 3 of 3

#### RH100-40.000-15-F-3030-EXT-TR

#### MARKING

R40.000 xxNFyw

- x Internal Production ID code
- y Year codew - Week code

Week code		
YEAR CODE		
Year	Code	
2015	5	
2016	6	
2017	7	
2018	8	
2019	9	
2020	0	
2021	1	
2022	2	
2023	3	
2024	4	
2025	5	

	ALPHA WEEK CODE TABLE				
Week	Code	Week	Code	Week	Code
1	а	19	s	37	K
2	b	20	t	38	L
3	с	21	u	39	М
4	d	22	v	40	Ν
5	е	23	w	41	0
6	f	24	х	42	Р
7	g	25	У	43	Q
8	h	26	Z	44	R
9	i	27	А	45	S
10	j	28	В	46	Т
11	k	29	С	47	U
12	1	30	D	48	V
13	m	31	E	49	W
14	n	32	F	50	Х
15	0	33	G	51	Y
16	р	34	Н	52	Z
17	q	35	Ι		
18	r	36	J		

## APPROVAL

DRAWN BY	XLiu, February 20, 2020
APPROVED BY	JIvens, February 20, 2020
REVISION	A, Initial Release

Raltron Electronics / RAMI Technology USA, LLC, including its affiliates, employees, agents and other persons acting on its behalf (collectively Raltron/RAMI Tech), disclaim any and all liability for any errors or inaccuracies contained in this data sheet. While Raltron/RAMI Tech has made every reasonable effort ensure the accuracy of all product information, specifications and data contained herein, Raltron/RAMI Tech has made every reasonable effort ensure the accuracy of all product information, specifications and data contained herein, Raltron/RAMI Tech hoses not guarantee that the information is accurate, reliable or current. The product information is provided only for reference purposes only and is subject to change, correction or revision, at any time withhout notice. Raltron/RAMI Tech hoses sume any liability arising out of an application or use of any product described herein and disclaims any warranties expressed or implied. The user of products in such applications shall assume all risks of such use and will agree to hold Raltron/RAMI Tech, harmless against all damages.

Copyright © 2016, Raltron Electronics / RAMI Technology USA, LLC. All rights reserved. No part of this document may be reproduced in any form without the prior written permission of Raltron Electronics / RAMI Technology USA, LLC.