## SIEMENS

## Data sheet

## US2:14DUC12FJ



Non-reversing motor starter, Size 1, Single phase full voltage, Solid-state overload relay, OLR amp range 3-12A, 24VAC 50-60Hz coil, Non-combination type, Enclosure type 4X fiberglass, Water/dust tight noncorrosive, Standard width enclosure

| product brand name   | Class 14                                 |
|--|--|
| design of the product  | Full-voltage non-reversing motor starter |
| special product feature  | ESP200 overload relay                    |
| General technical data   |  |
| weight [lb]  | 14 lb                                    |
| Height x Width x Depth [in]  | 15 × 12 × 7 in                           |
| touch protection against electrical shock                                  | (NA for enclosed products)               |
| installation altitude [ft] at height above sea level maximum               | 6560 ft                                  |
| ambient temperature [°F]   |  |
| <ul> <li>during storage</li> </ul>   | -22 +149 °F                              |
| <ul> <li>during operation</li> </ul>                                       | -4 +104 °F                               |
| ambient temperature  |  |
| <ul> <li>during storage</li> </ul>   | -30 +65 °C                               |
| during operation   | -20 +40 °C                               |
| country of origin  | USA                                      |
| Horsepower ratings   |  |
| yielded mechanical performance [hp] for single-phase AC motor              |  |
| <ul> <li>at 115 V rated value</li> </ul>                                   | 0.25 hp                                  |
| <ul> <li>at 200/208 V rated value</li> </ul>                               | 0.5 hp                                   |
| <ul> <li>at 220/230 V rated value</li> </ul>                               | 0.5 hp                                   |
| Contactor  |  |
| size of contactor  | NEMA controller size 1                   |
| number of NO contacts for main contacts                                    | 2  |
| operating voltage for main current circuit at AC at 60 Hz maximum          | 240 V                                    |
| operational current at AC at 600 V rated value                             | 27 A                                     |
| mechanical service life (switching cycles) of the main<br>contacts typical | 1000000                                  |
| Auxiliary contact  |  |
| number of NC contacts at contactor for auxiliary contacts                  | 0  |
| number of NO contacts at contactor for auxiliary contacts                  | 1  |
| number of total auxiliary contacts maximum                                 | 8  |
| contact rating of auxiliary contacts of contactor according to UL          | 10A@600VAC (A600), 5A@600VDC (P600)      |
| Coil   |  |
| type of voltage of the control supply voltage                              | AC                                       |
| control supply voltage   |  |
| • at AC at 50 Hz rated value   | 24 V                                     |

| • at AC at 60 Hz rated value  | 24 V   |
|---|--|
| holding power at AC minimum   | 8.6 W  |
| apparent pick-up power of magnet coil at AC   | 218 VA                                       |
| apparent holding power of magnet coil at AC   | 25 VA  |
| operating range factor control supply voltage rated value   | 0.85 1.1                                     |
| of magnet coil percental drop-out voltage of magnet coil related to the   | 50 %   |
| input voltage   |  |
| ON-delay time   | 19 29 ms                                     |
| OFF-delay time  | 10 24 ms                                     |
| Overload relay  |  |
| product function  |  |
| <ul> <li>overload protection</li> </ul>   | Yes  |
| <ul> <li>phase failure detection</li> </ul>   | Yes  |
| <ul> <li>asymmetry detection</li> </ul>   | Yes  |
| <ul> <li>ground fault detection</li> </ul>  | Yes  |
| test function   | Yes  |
| external reset  | Yes  |
| reset function  | Manual, automatic and remote                 |
| trip class  | CLASS 5 / 10 / 20 (factory set) / 30         |
| adjustable current response value current of the current-<br>dependent overload release                               | 3 12 A                                       |
| tripping time at phase-loss maximum   | 3 s  |
| relative repeat accuracy  | 1 %  |
| product feature protective coating on printed-circuit board   | Yes  |
| number of NC contacts of auxiliary contacts of overload   | 1  |
| relay   |  |
| number of NO contacts of auxiliary contacts of overload relay   | 1  |
| operational current of auxiliary contacts of overload relay   |  |
| • at AC at 600 V  | 5 A  |
| • at DC at 250 V  | 1 A  |
| contact rating of auxiliary contacts of overload relay according to UL  | 5A@600VAC (B600), 1A@250VDC (R300)           |
| insulation voltage (Ui)   |  |
| <ul> <li>with single-phase operation at AC rated value</li> </ul>   | 600 V  |
| <ul> <li>with multi-phase operation at AC rated value</li> </ul>  | 300 V  |
| Enclosure   |  |
| degree of protection NEMA rating  | 4X, fiber glass                              |
| design of the housing   | Dust-tight, watertight & corrosion resistant |
| Mounting/wiring   |  |
| mounting position   | Vertical                                     |
| fastening method  | Surface mounting and installation            |
|   | Screw-type terminals                         |
| type of electrical connection for supply voltage line-side  | 51   |
| tightening torque [lbf·in] for supply<br>type of connectable conductor cross-sections at line-side                    | 35 35 lbf·in<br>1x(14 - 2 AWG)               |
| at AWG cables single or multi-stranded<br>temperature of the conductor for supply maximum                             | 75 °C  |
| permissible   |  |
| material of the conductor for supply  | AL or CU                                     |
| type of electrical connection for load-side outgoing feeder   | Screw-type terminals                         |
| tightening torque [lbf·in] for load-side outgoing feeder  | 35 35 lbf·in                                 |
| type of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi-<br>stranded | 1x(14 - 2 AWG)                               |
| temperature of the conductor for load-side outgoing feeder maximum permissible  | 75 °C  |
| material of the conductor for load-side outgoing feeder   | AL or CU                                     |
| type of electrical connection of magnet coil  | screw-type terminals                         |
| tightening torque [lbf·in] at magnet coil   | 5 12 lbf·in                                  |
| type of connectable conductor cross-sections of magnet<br>coil at AWG cables single or multi-stranded                 | 2 x (16 - 12 AWG)                            |
| temperature of the conductor at magnet coil maximum   | 75 °C  |

| permissible   |   |
|---|---|
| -   | CU  |
| material of the conductor at magnet coil  |   |
| type of electrical connection for auxiliary contacts  | screw-type terminals<br>10 15 lbf·in                |
| tightening torque [lbf·in] at contactor for auxiliary contacts  |   |
| type of connectable conductor cross-sections at contactor<br>at AWG cables for auxiliary contacts single or multi-<br>stranded  | 1 x (12 AWG), 2 x (16 - 14 AWG), 2 x (18 - 16 AWG)  |
| temperature of the conductor at contactor for auxiliary<br>contacts maximum permissible   | 75 °C   |
| material of the conductor at contactor for auxiliary contacts   | CU  |
| type of electrical connection at overload relay for auxiliary<br>contacts   | screw-type terminals                                |
| tightening torque [lbf·in] at overload relay for auxiliary<br>contacts  | 7 10 lbf·in   |
| type of connectable conductor cross-sections at overload relay at AWG cables for auxiliary contacts single or multi-<br>stranded  | 2 x (20 - 14 AWG)                                   |
| temperature of the conductor at overload relay for auxiliary contacts maximum permissible   | 75 °C   |
| material of the conductor at overload relay for auxiliary contacts  | CU  |
| Short-circuit current rating  |   |
| design of the fuse link for short-circuit protection of the<br>main circuit required  | 10kA@600V (Class H or K); 100kA@600V (Class R or J) |
| design of the short-circuit trip  | Thermal magnetic circuit breaker                    |
| breaking capacity maximum short-circuit current (Icu)   |   |
| • at 240 V  | 14 kA   |
| • at 480 V  | 10 kA   |
| • at 600 V  | 10 kA   |
| certificate of suitability  | NEMA ICS 2; UL 508; CSA 22.2, No.14                 |
| Further information   |   |
| Industrial Controls - Product Overview (Catalogs, Brochures,)<br>www.usa.siemens.com/iccatalog<br>Industry Mall (Online ordering system)<br>https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:14DUC12FJ |   |
| Service&Support (Manuals, Certificates, Characteristics, FAQs,)<br>https://support.industry.siemens.com/cs/US/en/ps/US2:14DUC12FJ   |   |
| Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros,)<br>http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:14DUC12FJ⟨=en<br>Certificates/approvals          |   |

https://support.industry.siemens.com/cs/US/en/ps/US2:14DUC12FJ/certificate

last modified:

11/29/2021 🖸