SIEMENS

Data sheet

US2:14FUF32BS



Non-reversing motor starter, Size 2, Three phase full voltage, Solid-state overload relay, OLR amp range 13-52A, 24VDC coil, Non-combination type, Enclosure type 1, Indoor general purpose use, Standard width enclosure

| Fi | gu | re s | sin | nil | ar | |
|----|----|------|-----|-----|----|--|
| | | | | | | |


| product brand name | Class 14 | | |
|---|--|--|--|
| design of the product | Full-voltage non-reversing motor starter | | |
| special product feature | ESP200 overload relay | | |
| General technical data | | | |
| weight [lb] | 13 lb | | |
| Height x Width x Depth [in] | 14 × 8 × 7 in | | |
| touch protection against electrical shock | (NA for enclosed products) | | |
| installation altitude [ft] at height above sea level maximum | 6560 ft | | |
| ambient temperature [°F] | | | |
| during storage | -22 +149 °F | | |
| during operation | -4 +104 °F | | |
| ambient temperature | | | |
| during storage | -30 +65 °C | | |
| during operation | -20 +40 °C | | |
| country of origin | USA | | |
| Horsepower ratings | | | |
| yielded mechanical performance [hp] for 3-phase AC motor | | | |
| • at 200/208 V rated value | 10 hp | | |
| • at 220/230 V rated value | 15 hp | | |
| • at 460/480 V rated value | 25 hp | | |
| • at 575/600 V rated value | 25 hp | | |
| Contactor | | | |
| size of contactor | NEMA controller size 2 | | |
| number of NO contacts for main contacts | 3 | | |
| operating voltage for main current circuit at AC at 60 Hz maximum | 600 V | | |
| operational current at AC at 600 V rated value | 45 A | | |
| mechanical service life (switching cycles) of the main contacts typical | 1000000 | | |
| Auxiliary contact | | | |
| number of NC contacts at contactor for auxiliary contacts | 0 | | |
| number of NO contacts at contactor for auxiliary contacts | 1 | | |
| number of total auxiliary contacts maximum | 7 | | |
| contact rating of auxiliary contacts of contactor according to UL | 10A@600VAC (A600), 5A@600VDC (P600) | | |
| Coil | | | |
| type of voltage of the control supply voltage | DC | | |
| control supply voltage | | | |

| at DC rated value | 24.1/ |
|---|---|
| | 24 V 0 W |
| holding power at AC minimum | |
| apparent pick-up power of magnet coil at AC | 163 VA 5.5 VA |
| apparent holding power of magnet coil at AC | |
| operating range factor control supply voltage rated value of magnet coil | 0.85 1.1 |
| percental drop-out voltage of magnet coil related to the input voltage | 25 % |
| ON-delay time | 21 21 ms |
| OFF-delay time | 11 11 ms |
| Overload relay | |
| product function | |
| overload protection | Yes |
| phase failure detection | Yes |
| asymmetry detection | Yes |
| ground fault detection | Yes |
| test function | Yes |
| external reset | Yes |
| reset function | Manual, automatic and remote |
| | |
| trip class | CLASS 5 / 10 / 20 (factory set) / 30 13 52 A |
| adjustable current response value current of the current- dependent overload release | 13 52 A |
| tripping time at phase-loss maximum | 3 s |
| relative repeat accuracy | 1 % |
| product feature protective coating on printed-circuit board | Yes |
| number of NC contacts of auxiliary contacts of overload relay | 1 |
| number of NO contacts of auxiliary contacts of overload relay | 1 |
| operational current of auxiliary contacts of overload relay | |
| • at AC at 600 V | 5 A |
| • at DC at 250 V | 1 A |
| contact rating of auxiliary contacts of overload relay according to UL | 5A@600VAC (B600), 1A@250VDC (R300) |
| insulation voltage (Ui) | |
| with single-phase operation at AC rated value | 600 V |
| with multi-phase operation at AC rated value | 300 V |
| Enclosure | |
| degree of protection NEMA rating | 1 |
| design of the housing | Indoor general purpose use |
| | |
| Mounting/wiring | |
| mounting position | Vertical |
| fastening method | Surface mounting and installation |
| type of electrical connection for supply voltage line-side | Box lug |
| tightening torque [lbf·in] for supply | 45 45 lbf·in |
| type of connectable conductor cross-sections at line-side at AWG cables single or multi-stranded | 1x(14 - 2 AWG) |
| temperature of the conductor for supply maximum permissible | 75 °C |
| material of the conductor for supply | AL or CU |
| type of electrical connection for load-side outgoing feeder | Box lug |
| tightening torque [lbf·in] for load-side outgoing feeder | 45 45 lbf·in |
| type of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi- stranded | 1x(14 - 2 AWG) |
| temperature of the conductor for load-side outgoing feeder maximum permissible | 75 °C |
| material of the conductor for load-side outgoing feeder | AL or CU |
| type of electrical connection of magnet coil | screw-type terminals |
| tightening torque [lbf·in] at magnet coil | 5 12 lbf·in |
| type of connectable conductor cross-sections of magnet coil at AWG cables single or multi-stranded | 2 x (16 - 12 AWG) |
| temperature of the conductor at magnet coil maximum | 75 °C |

| permissible | | | | |
|---|---|--|--|--|
| material of the conductor at magnet coil | CU | | | |
| type of electrical connection for auxiliary contacts | screw-type terminals | | | |
| tightening torque [lbf·in] at contactor for auxiliary contacts | 10 15 lbf·in | | | |
| type of connectable conductor cross-sections at contactor at AWG cables for auxiliary contacts single or multi- stranded | 1 x (12 AWG), 2 x (16 - 14 AWG), 2 x (18 - 16 AWG) | | | |
| temperature of the conductor at contactor for auxiliary contacts maximum permissible | 75 °C | | | |
| material of the conductor at contactor for auxiliary contacts | CU | | | |
| type of electrical connection at overload relay for auxiliary contacts | screw-type terminals | | | |
| tightening torque [lbf·in] at overload relay for auxiliary contacts | 7 10 lbf·in | | | |
| type of connectable conductor cross-sections at overload relay at AWG cables for auxiliary contacts single or multi- stranded | 2 x (20 - 14 AWG) | | | |
| temperature of the conductor at overload relay for auxiliary contacts maximum permissible | 75 °C | | | |
| material of the conductor at overload relay for auxiliary contacts | CU | | | |
| Short-circuit current rating | | | | |
| design of the fuse link for short-circuit protection of the main circuit required | 10kA@600V (Class H or K); 100kA@600V (Class R or J) | | | |
| design of the short-circuit trip | Thermal magnetic circuit breaker | | | |
| breaking capacity maximum short-circuit current (Icu) | | | | |
| • at 240 V | 14 kA | | | |
| • at 480 V | 10 kA | | | |
| • at 600 V | 10 kA | | | |
| certificate of suitability | NEMA ICS 2; UL 508; CSA 22.2, No.14 | | | |
| Further information | | | | |
| Industrial Controls - Product Overview (Catalogs, Brochures,) www.usa.siemens.com/iccatalog Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:14FUF32BS | | | | |
| Service&Support (Manuals, Certificates, Characteristics, FAQs,) https://support.industry.siemens.com/cs/US/en/ps/US2:14FUF32BS | | | | |

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:14FUF32BS&lang=en

Certificates/approvals https://support.industry.siemens.com/cs/US/en/ps/US2:14FUF32BS/certificate



last modified:

11/29/2021 🖸