

SG73S-RT

endured surge voltage flat chip resistors (anti-surge, anti-sulfuration)




features



- Excellent anti-sulfuration characteristic due to using high sulfuration-proof inner top electrode material
- Superior to RK73 series chip resistors in pulse withstanding voltage and high power
- SG73S (for pulse) are able to select resistance tolerance is available from ±0.5%
- Suitable for both reflow and flow solderings
- Products with lead-free terminations meet EU RoHS requirements. EU RoHS regulation is not intended for Pb-glass contained in electrode, resistor element and glass.
- AEC-Q200 Tested

dimensions and construction



Туре	Dimensions inches (mm)								
(Inch Size Code)	L	W	С	d	t				
SG73S 1E, (0402)	.039 +.004 002 (1.0 +0.1)	.020±.002 (0.5±0.05)	.006±.004 (0.15±0.1)	.010 +.002 004 (0.25 +0.05 -0.1	.014±.002 (0.35±0.05)				
SG73S 1J, (0603)	.063±.008 (1.6±0.2)	.031±.004 (0.8±0.1)	.012±.004 (0.3±0.1)	.012±.004 (0.3±0.1)	.018±.004 (0.45±0.1)				
SG73S 2A, (0805)	.079±.008 (2.0±0.2)	.049±.004 (1.25±0.1)	.012 +.008004 (0.3 +0.2)	.012 +.008004 (0.3 +0.2)	.020±.004 (0.5±0.1)				
SG73S 2B, (1206)	.126±.008	.063±.008 (1.6±0.2)	.016 +.008	.016 +.008	.024±.004				
SG73S 2E, SG73S 2E1 (1210)	(3.2±0.2)	.102±.008 (2.6±0.2)	(0.4 +0.2)	(0.4 +0.2)	(0.6±0.1)				

ordering information







Termination Material					
T: Sn					

TD							
Packaging							
TP: 0402, 0603, 0805: 7" 2mm							


TD: 0603, 0805, 1206, 1210: 7" 4mm pitch punched paper

TE: 0805, 1206, 1210: 7" 4mm embossed plastic For further information on

For further information on packaging, please refer to Appendix A

Nominal Resistance ±0.5%, ±1%: 3 significant figures

+ 1 multiplier ±2%, ±5%: 2 significant figures + 1 multiplier "R" indicates decimal on value <10Ω





SG73S-RT

endured surge voltage flat chip resistors (anti-surge, anti-sulfuration)

applications and ratings

Part	Power	Rated	Rated Terminal	T.C.R.		Resistance Range			Maximum	Maximum	Operating
Designation	Rating	Ambient Temp.	Part (ppm/°C) Temp. (ppm/°C)	D: ±0.5% E-24, E-96	F: ±1% E-24, E-96	G: ±2% E-24	J: ±5% E-24	Working Voltage	Overload Voltage	Temp. Range	
00700 45	0.125W	- 70°C	125°C	222		10Ω - 1ΜΩ	10Ω - 10ΜΩ		75V	100V	-55°C to +155°C
SG73S 1E	0.2W*2		105°C	±200							
SG73S 1J	0.2W	- 70°C	135°C	±100*1						200V	
	0.33W*2		125°C						150V		
SG73S 2A	0.25W	70°C	125°C							600V (800V)*3	
	0.5W*2		100°C	±200	100Ω - 1ΜΩ			1Ω - 10ΜΩ	400V		
SG73S 2B	0.33W	70°C	125°C	±200						400V	
	0.75W*2		105°C								
SG73S 2E	0.5W	70°C	125°C	±200					200V		
	0.75W*2		110°C								
SG73S 2E1	1.0W*2	70°C	95°C	±200							


^{*}¹ Cold T.C.R. (-55°C ~ +25°C) is ±150x10°/K *² If you want to use the rated power of *², *³ please reference below. *³ Applies when power rating is 0.4W or lower.


Rated voltage = $\sqrt{\text{Power rating x resistance value}}$ or max. working voltage, whichever is lower


If any questions should arise whether to use the "Rated Ambient Temperature" or the "Rated Terminal Part Temperature," please give priority to the "Rated Terminal Part Temperature." Prior to use and for more details refer to "Introduction of the derating curves on the terminal part temperature" in the beginning of the catalog. Also, contact KOA prior to usage and for the max. working voltage and max. overload voltage.


environmental applications

Derating Curve









For resistors operated at a terminal part temperature of described for each size or above, a power rating shall be derated in accordance with the derating curve.

Please refer to "Introduction of the derating curve based on the terminal part temperature" in the beginning of our catalog before use.

*2, *3 If you want to use the rated power of *2, *3, please use the derating curve based on the terminal part temperature on the right hand side.

Additional environmental applications can also be found at www.koaspeer.com





endured surge voltage flat chip resistors (anti-surge, anti-sulfuration)

environmental applications (continued)

Performance Characteristics

	Requirement Δ R ±(%+0.1Ω)				
Parameter	Limit	Typical	Test Method		
Resistance	Within specified tolerance	_	25°C		
T.C.R.	Within specified T.C.R.	_	+25°C/-55°C and +25°C/+125°C		
Overload (Short time)	±2%	±0.5%	Rated Voltage x 2.5 for 5 seconds (2A: 0.4W, 0.5W; 2B: 0.75W; 2E: 0.75W; 2E1: 1W x 2 for 5 seconds)		
Resistance to Solder Heat	±1%	±0.75%	260°C ± 5°C, 10 seconds ± 1 second		
Rapid Change of Temperature	±0.5%	±0.3%	-55°C (30 minutes), +125°C (30 minutes), 100 cycles		
Moisture Resistance	±3%	±0.75%	40°C ± 2°C, 90%~95%RH, 1000 hours; 1.5 hr ON, 0.5 hr OFF cycle		
Endurance at 70°C	±3%	±0.75%	70°C ± 2°C, 1000 hours, 1.5 hr ON, 0.5 hr OFF cycle		
High Temperature Exposure	±1%	±0.3%	+155°C, 1000 hours		
Sulfuration Test	±5%	±0.2%	Soaked in industrial oil with 3.5% sulfur concentration 105°C ± 3°C, 500 hours		

Please refer to conventional products for characteristic data such as temperature rise.