
Assembly Instructions


1) Strip the cable to the dimensions shown, cutting the centre conductor at approximately a 30° angle. Take care not to nick the centre conductor or braid. Cutting the centre conductor at 30° facilitates easy entry of the conductor into the connector.


A = 6.4mm

B = 12.7mm




2) Twist the braid in a clockwise direction so that a minimum of 1.0mm dielectric is shown. Make sure to avoid loose or stray strands that could cause short circuits.






3) Insert the centre conductor into the guide hole in the rear insulator of the connector.



4) Firmly push the cable as far forward as possible and screw the connector hex back end onto the cable in a clockwise direction until it stops.



CAD Issue	SN	2	01 Nov 01
First Issue	CBB	1	23 Jan 98
DESCRIPTION OF REVISION	APPVD	ISS	DATE



Cinch Connectivity Solutions, Ltd 11 Bilton Road Chelmsford Essex CM1 2UP, England

Essex CM1 2UP, England T: +44 (0) 1245 342060 F: +44 124 535 8938

	SCALE: Not To Scale	DRAWN BY:	S Nash
DIMENSIONS: mm	CHECKED BY:	P Couzens	
TOLERANCES:		APPROVED BY:	M Nielsen
		DATE:	01 Nov 01

DESCRIPTION:

Stripping and Assembly Instructions for BNC Twist On Jack DRAWING NUMBER:

VAIB3301

PAGE: 1 OF 1