# **Low Pass Filter**

#### \*DC to 530 MHz $50\Omega$

#### **Maximum Ratings**

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input*	8.5W max. at 25°C
DC Current Input to Output	0.5A max. at 25°C

<sup>\*</sup> Passband rating, derate linearly to 3.5W at 100°C ambient. Permanent damage may occur if any of these limits are exceeded

#### **Features**

- rugged uni-body construction, small size
- excellent power handling, 8.5W
- temperature stable
- protected by U.S. Patent 6,943,646

#### • 7 sections

- · low cost

# **Applications**


- harmonic rejection
- transmitters/receivers
- lab use

## Electrical Specifications at 25°C

PASSBAND (MHz)	fco, MHz Nom.	STOP BAND (MHz) (loss, dB)		VSWR (:1)		NO. OF SECTIONS	
(loss < 1.2 dB)	(loss 3 dB)	f 20	40	fr 20	Stopband	Passband	
Max.	Тур.	Min.	Typ.	Тур.	Тур.	Тур.	
*DC-530	700	820	945-3000	6000	20	1.2	7

<sup>\*</sup> Not for use with DC voltage at input and output ports


## **Outline Drawing**



### Outline Dimensions (inch )

wt	Е	D	В
grams	.312	1.43	.410
10.0	7 92	36 32	10 41

#### typical frequency response



#### electrical schematic

VLF-530+

Generic photo used for illustration purposes only

CASE STYLE: FF704


+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site

for RoHS Compliance methodologies and qualifications

Connectors


Model


VLF-530+



## Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
1	0.05	1.01
100	0.22	1.03
300	0.41	1.05
530	0.83	1.08
650	1.78	1.50
700	3.52	2.31
740	8.75	5.42
775	17.33	10.43
820	34.05	15.13
945	43.81	22.29
1000	52.72	25.94
2000	70.84	46.96
3000	42.58	43.44
5500	24.42	26.74
6000	23.25	30.49





A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp