

# wide terminal type flat chip resistors (low resistance)






#### features

- Wide-side termination (reverse-geometry) type flat chip resistor
- High reliability and performance with T.C.R. ±100 x 10<sup>-6</sup>/K, resistance tolerance ±0.5%
- Suitable for both reflow and flow solderings
- Products with lead-free terminations meet EU RoHS requirements. EU RoHS regulation is not intended for Pb-glass contained in electrode, resistor element and glass.
- AEC-Q200 Tested

#### dimensions and construction



Туре	Dimensions inches (mm)					
(Inch Size Code)	L W		С	d	t	
2A (0508)	.049±.006 (1.25±0.15)	.079±.006 (2.0±0.15)	.012±.008 (0.3±0.2)	.014±.008 (0.35±0.2)	.022±.004 (0.55±0.1)	
2B (0612)	.063±.006 (1.6±0.15)	.126±.008 (3.2±0.2)	.012±.008 (0.3±0.2)	.018±.006 (0.45±0.15)	.024±.004 (0.6±0.1)	
2H (1020)	.098±.006 (2.5±0.15)	.197±.006 (5.0±0.15)	.016±.008 (0.4±0.2)			
2J* (1218)	.122±.006 (3.1±0.15)	.181±.006 (4.6±0.15)	.016±.008 (0.4±0.2)	.030±.006 (0.75±0.15)		
3A (1225)	.122±.006 (3.1±0.15)	.252±.006 (6.3±0.15)	.018±.008 (0.45±0.2)			

100


60

40


Please refer to "Introduction of the derating curve based on the terminal part temperature" in the

If you want to use at rated power (\*1), use derating curves based on the terminal part temperature

### **Derating Curve**



For resistors operated at an ambient temperature of  $70^{\circ}\text{C}$  or above, a power rating shall be derated in accordance with the above derating curve.




oli de de la composition del composition de la composition de la composition de la composition de la composition del composition de la com

WK73S2B (1W), WK73S3A (2W)

2B. 3A (115°C)

#### ordering information



Size

2A: 1W
2B: 0.75W, 1W
2H: 1W
2J\*: 1W
3A: 1.5W, 2W

# Termination Material T: Sn

# Packaging TD: 0508, 0612: 7" 4mm pitch

beginning of our catalog before use.

on the right side graph.

punched paper
TE: 1020, 1218, 1225:
7" embossed plastic
For further information on

For further information on packaging, please refer to Appendix A

# Nominal

33L0


Resistance

 $\pm$ 1%: 3 significant figures + 1 multiplier "R" indicates decimal on value <100 $\Omega$ 

 $\pm 5\%$ : 2 significant figures + 1 multiplier "R" indicates decimal on values <10  $\!\Omega$ 

All values less than 0.1  $\!\Omega$  (100m  $\!\Omega\!$  ) are expressed in m  $\!\Omega\!$  with "L" as decimal.

Ex:  $33m\Omega$ , 1% = 33L0



\* WK73S2J Not Recommended for New Design Recommended replacement WK73S2H

Specifications given herein may be changed at any time without prior notice. Please confirm technical specifications before you order and/or use.

4/05/23





## wide terminal type flat chip resistors (low resistance)


## applications and ratings

Part Designation	Power Rating	Rated Ambient Temp.	Rated Terminal Part Temp.	T.C.R. (X 10°/K)	D±0.5% E-24/E-96	Resistance Range (Ω) F±1% E-24/E-96	J±5% E-24	Operating Temp. Range
<b>WK73S2A</b> 1.0W <sup>1</sup>				±100	_	1 - 9.76	1 - 9.1	
	70°C	125°C	0~+200	_	30m - 976m	30m - 910m		
				0~+300		20m - 29.4m	20m - 27m	-55°C to +155°C
	0.75W	70°C	125°C	±100	430m - 9.76	430m - 9.76	430m - 9.1	
				±200	_	30m - 422m	30m - 390m	
WK73S2B				±800	_	_	10m - 27m	
WK/332B			115°C	±100	430m - 9.76	430m - 9.76	430m - 9.1	
	1.0W¹	70°C		±200	_	30m - 422m	30m - 390m	
				±800	_	_	10m - 27m	
		70°C	125°C	±100	_	220m - 9.76	220m - 9.1	
WK73S2H	WK73S2H 1.0W			±200	_	27m - 215m	27m - 200m	
				±800	_	_	10m - 24m	
		70°C	100°C	±100	_	240m - 9.76	240m - 9.1	
WK73S2J*	<b>WK73S2J*</b> 1.0W			±200	_	33m - 237m	33m - 220m	
				±800	_	_	10m - 30m	
1.5W			±100	_	360m - 9.76	360m - 9.1		
	4 5\\/	70°C	125°C	±200	_	33m - 357m	33m - 330m	
	/0°C	125-0	±300	_	22m - 32.4m	22m - 30m	1	
				±800	_	_	10m - 20m	
WK/353A	2.0W¹	70°C	115°C -	±100	_	360m - 9.76	360m - 9.1	
				±200	_	33m - 357m	33m - 330m	
				±300	_	22m - 32.4m	22m - 30m	
				±800	_	_	10m - 20m	

Rated voltage =  $\sqrt{\text{Power rating x resistance value}}$ 


#### **Temperature Rise**

# \* WK73S2J Not Recommended for New Design Recommended replacement WK73S2H



Regarding the temperature rise, the value of the temperature varies per conditions and board for use since the temperature is measured under our measuring conditions.

# One-Pulse Limiting Electric Power WK73S 2A-3A



Please ask us about the resistance characteristic of continuous applied pulse.

# environmental applications

#### **Performance Characteristics**

	Requirement $\Delta$	R ±(%+0.005Ω)	
Parameter	Limit	Typical	Test Method
Resistance	Within specified tolerance	_	25°C
T.C.R.	Within specified T.C.R.	_	+25°C/-55°C and +25°C/+125°C
Overload (Short time)	±2%	±0.2%	Rated voltage x2.5 for 5 seconds (WK73S2A, WK73S2B (1W), WK73S3A (2W): Rated voltage x2.0 for 5 seconds)
Resistance to Solder Heat	±1%	±0.2%	260°C ± 5°C, 10 seconds ± 1 second
Bending Test	±1%	±0.1%	Holding point 90mm, Bending 1 time, Bending 5mm
Rapid Change of Temperature	±2%	±1%	-55°C (30 minutes), +125°C (30 minutes), 1000 cycles
Moisture Resistance	±2%	±0.2%	40°C ± 2°C, 90%-95% RH, 1000 hours, 1.5 hr ON, 0.5 hr OFF cycle
Endurance at 70°C	±2%	±0.2%	70°C ± 2°C or rated terminal part temperature ± 2°C, 1000 hours, 1.5 hr ON, 0.5 hr OFF cycle
High Temperature Exposure	±2%: WK73S (±5%) ±1%: all others	±0.5%: WK73S (±5%) ±0.2%: all others	+155°C, 1000 hours

PCB: FR-4t = 1.6mm

2: Termina

Additional environmental applications can also be found at www.koaspeer.com

Specifications given herein may be changed at any time without prior notice. Please confirm technical specifications before you order and/or use.

If you want to use at rated power use derating curves based on the terminal part temperature on the right side graph located on previous page. If any questions arise whether to use the "Rated Ambient Temperature" or the "Rated Terminal Part Temperature", please give priority to the "Rated Terminal Part Temperature." For more details refer to the "Introduction of the derating curves based on the terminal part temperature" in the beginning of the catalog