
| | 12 | | 11 | 10 | | | |
|---|-------------|----|------------|------|--------|--|--|
| | PART NO. | | ENG NO. | PI | LATING | | |
| Н | | | | | | | |
| | 008-56-0113 | 24 | 177-G | 565 | | | |
| | 008-56-0114 | 24 | 177-GL | Į | 565 | | |
| | 008-50-0109 | 24 | 77-(P909) | F | >909 | | |
| | 008-50-0110 | 24 | 77-(P909)L | P909 | | | |
| | | | | | | | |
| | | | | | | | |




CUT-OFF DIM.


9

8

8



7



NOTES:

G

F


D

С

B

- 1. MATERIAL: SEE LEGEND
- 2. FINISH: P909: OVERALL HOT TIN DIP: (0.00254)/.000100 MIN. 565: SELECT GOLD: (0.00051)/.000020 MIN. OVERALL NICKEL: (0.00076)/.000030 MIN.
 - OVERALL GOLD FLASH: (0.00005)/.000002 MIN.
- 3. PRODUCT SPECIFICATION: PS-08-50
- 4. PACKAGING SPECIFICATION: LOOSE TERMINALS: PK-2759-001
- CHAIN FORM TERMINALS: PER PK-2759-002
- 5. CRIMP ACCEPTS 18 TO 24 GA. WIRE WITH (2.79)/.110 MAX. INSULATION DIA.
- 6. TERMINAL FOR USE IN 2139 AND 3069 SERIES HOUSINGS WITH (2.54)/.100 MAX. INSULATION DIAMETER AND 172159 SERIES HOUSINGS WITH (2.79)/.110 MAX. INSULATION DIAMETER.
- 7. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.
- 8. MATING TERMINALS TO ROUND PINS IS NOT RECOMMENDED.


| DOCUMENT STATUS | P1 | RELEASE DATE | 2018/10/05 | 09:56:19 | |
|--|----|--------------|------------|----------|---|
| FORMAT: Eng-lega-master-tb-prod-C REVISION: D DATE: 2018/01/18 | | 11 | 10 | | 9 |




6



6





| SYMBO | าร | | IS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION | | | | | | | | | | | | | |
|------------|--------------------------|----------------------------------|---|--------------------------------|--------------------------|-------------------|--------------|------------------------------|--------------------------|---------------|-----------------------------|-------|----------|----------|----------|---|
| | | DIMENSION UNIT | rs s | CALE | CURREN | T REV DES | C: NOTE 4 AD | DED | | | | | | | | |
| ¥ = | 0 | MM/IN | 1 | 1:1 | | | | molex | | | | | | | | |
| ₹ = | 7 = 0 GENERAL TOLERANCES | | | | | | | | | | | | | | | |
| v | | (UNLE | SS SPEC | IFIED) | | | | | | | | | | | | |
| ₩ = | 0 | | MM | INCH | EC NO: | 605479 | | | | Kł | K CRIMP T | ERMI | NAL | | | |
| <u></u> = | 0 | 4 PLACES | ± | ± | DRWN: | SS06 | | 2018/09/19 | | (3.96)/.156 C | 6 CENTERS 18 TO 24 AWG WIRE | | | | | |
| ~ | ~ | 3 PLACES | LACES ± ± 0.01 CHK'D: ISHWARG 2018/10/05 | | | | | | | | | | | | | |
| = | 0 | 2 PLACES | ± 0.25 | ± 0.014 | APPR: ISHWARG 2018/10/05 | | | | PRODUCT CUSTOMER DRAWING | | | | | | | |
| C = | 0 | 1 PLACE | ± 0.36 | ± | INITIAL | INITIAL REVISION: | | | | UMENT NUMBER | | | DOC TYPE | DOC PART | REVISION | Α |
| = | 0 | 0 PLACES | ± | ± | DRWN: SAMIEC | | 1995/03/02 | ² SD-2477-XXXX PS | | | | | 001 | יסא | | |
| _ | • | ANGULA | R TOL | ± 0.5 ° | APPR: | APPR: | | | | JD-24// | -\\\\ | | PSD | 001 | AD3 | |
| = | 0 | DRAFT WHERE APPLICABLE | | THIRD ANGLE PROJECTION DRAWING | | SERIES | MATE | ERIAL NUMBER | JMBER CUSTOMER SHE | | | | UMBER | | | |
| <u></u> = | 0 | MUST REMAIN WITHIN DIMENSIONS | | | | | C-SIZE | 2477 | 5 | SEE CHART | GENERA | AL MA | RKET | 1 C |)F 1 | |
| | | | | • | 4 | | <u> </u> | | | | | | 4 | | | |