SIEMENS

Data sheet

US2:17CUD92NH



Non-reversing motor starter, Size 0, Three phase full voltage, Solid-state overload relay, OLR amp range 5.5-22A, Combination type, 30A non-fusible disconnect, Enclosure NEMA type 4/12, Water/dust tight for outdoors, Standard width enclosure


Figuresi	imilar
----------	--------

product brand name	Class 17 & 25
design of the product	Full-voltage non-reversing motor starter with non-fusible disconnect
special product feature	ESP200 overload relay
General technical data	
Height x Width x Depth [in]	24 × 11 × 8 in
touch protection against electrical shock	(NA for enclosed products)
installation altitude [ft] at height above sea level maximum	6560 ft
ambient temperature [°F]	
 during storage 	-22 +149 °F
during operation	-4 +104 °F
ambient temperature	
 during storage 	-30 +65 °C
during operation	-20 +40 °C
Horsepower ratings	
yielded mechanical performance [hp] for 3-phase AC motor	
• at 200/208 V rated value	3 hp
• at 220/230 V rated value	3 hp
• at 460/480 V rated value	0 hp
 at 575/600 V rated value 	0 hp
Contactor	
size of contactor	NEMA controller size 0
number of NO contacts for main contacts	3
operational current at AC at 600 V rated value	18 A
mechanical service life (switching cycles) of the main contacts typical	1000000
Auxiliary contact	
number of NC contacts at contactor for auxiliary contacts	0
number of NO contacts at contactor for auxiliary contacts	1
number of total auxiliary contacts maximum	8
contact rating of auxiliary contacts of contactor according to UL	10A@600VAC (A600), 5A@600VDC (P600)
Coil	
type of voltage of the control supply voltage	AC
control supply voltage	
• at AC at 50 Hz rated value	380 440 V
• at AC at 60 Hz rated value	440 480 V
holding power at AC minimum	8.6 W
apparent pick-up power of magnet coil at AC	218 VA

apparent holding power of meanet asilist A.C.	25.1/4
apparent holding power of magnet coil at AC	25 VA 0.85 1.1
operating range factor control supply voltage rated value of magnet coil	
percental drop-out voltage of magnet coil related to the input voltage	50 %
ON-delay time	19 29 ms
OFF-delay time	10 24 ms
Overload relay	
product function	
overload protection	Yes
 phase failure detection 	Yes
 asymmetry detection 	Yes
ground fault detection	Yes
test function	Yes
 external reset 	Yes
reset function	Manual, automatic and remote
trip class	CLASS 5 / 10 / 20 (factory set) / 30
adjustable current response value current of the current- dependent overload release	5.5 22 A
make time with automatic start after power failure maximum	3 s
relative repeat accuracy	1 %
product feature protective coating on printed-circuit board	Yes
number of NC contacts of auxiliary contacts of overload	1
relay	
number of NO contacts of auxiliary contacts of overload relay	1
operational current of auxiliary contacts of overload relay	
• at AC at 600 V	5 A
● at DC at 250 V	1 A
contact rating of auxiliary contacts of overload relay	5A@600VAC (B600), 1A@250VDC (R300)
according to UL	
insulation voltage (Ui)	C00.1/
with single-phase operation at AC rated value	600 V
with multi-phase operation at AC rated value	300 V
Disconnect Switch	
response value of switch disconnector	30A / 600V
design of fuse holder	non-fusible
operating class of the fuse link	non-fusible
Enclosure	
degree of protection NEMA rating	4, 12
design of the housing	dustproof, waterproof & weatherproof
Mounting/wiring	
mounting position	vertical
fastening method	Surface mounting and installation
type of electrical connection for supply voltage line-side	Box lug
tightening torque [lbf·in] for supply	35 35 lbf·in
type of connectable conductor cross-sections at line-side at AWG cables single or multi-stranded	1x (14 2 AWG)
temperature of the conductor for supply maximum permissible	75 °C
material of the conductor for supply	AL or CU
type of electrical connection for load-side outgoing feeder	Screw-type terminals
tightening torque [lbf·in] for load-side outgoing feeder	20 20 lbf·in
type of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi- stranded	1x (14 2 AWG)
temperature of the conductor for load-side outgoing feeder	75 °C
maximum permissible	
maximum permissible material of the conductor for load-side outgoing feeder	AL or CU
· · · · · · · · · · · · · · · · · · ·	AL or CU Screw-type terminals
material of the conductor for load-side outgoing feeder	

type of connectable conductor cross-sections of magnet coil at AWG cables single or multi-stranded	2x (16 12 AWG)	
temperature of the conductor at magnet coil maximum permissible	75 °C	
material of the conductor at magnet coil	CU	
type of electrical connection for auxiliary contacts	Screw-type terminals	
tightening torque [lbf·in] at contactor for auxiliary contacts	10 15 lbf·in	
type of connectable conductor cross-sections at contactor at AWG cables for auxiliary contacts single or multi- stranded	1x (12 AWG), 2x (16 14 AWG), 2x (18 16 AWG)	
temperature of the conductor at contactor for auxiliary contacts maximum permissible	75 °C	
material of the conductor at contactor for auxiliary contacts	CU	
type of electrical connection at overload relay for auxiliary contacts	Screw-type terminals	
tightening torque [lbf·in] at overload relay for auxiliary contacts	7 10 lbf·in	
type of connectable conductor cross-sections at overload relay at AWG cables for auxiliary contacts single or multi- stranded	2x (20 14 AWG)	
temperature of the conductor at overload relay for auxiliary contacts maximum permissible	75 °C	
material of the conductor at overload relay for auxiliary contacts	CU	
Short-circuit current rating		
design of the fuse link for short-circuit protection of the main circuit required	10kA@600V (Class H or K); 100kA@600V (Class R or J)	
certificate of suitability	NEMA ICS 2; UL 508; CSA 22.2, No.14	
Further information		
Industrial Controls - Product Overview (Catalogs, Brochures,)		
www.usa.siemens.com/iccatalog		
Industry Mall (Online ordering system)		
https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:17CUD92NH		
Service&Support (Manuals, Certificates, Characteristics, FAQs,) https://support.industry.siemens.com/cs/US/en/ps/US2:17CUD92NH		
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros,) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:17CUD92NH⟨=en		

Certificates/approvals https://support.industry.siemens.com/cs/US/en/ps/US2:17CUD92NH/certificate



D68782001

last modified:

1/25/2022 🖸