SIEMENS

Data sheet US2:17DUB82NH



Non-reversing motor starter, Size 1, Three phase full voltage, Solid-state overload relay, OLR amp range 0.75-3.4A, Combination type, 30A non-fusible disconnect, Enclosure NEMA type 4/12, Water/dust tight for outdoors, Extra-wide enclosure

Figure similar

product brand name	Class 17 & 25	
design of the product	Full-voltage non-reversing motor starter with non-fusible disconnect	
special product feature	ESP200 overload relay	
General technical data		
Height x Width x Depth [in]	24 × 20 × 8 in	
touch protection against electrical shock	(NA for enclosed products)	
installation altitude [ft] at height above sea level maximum	6560 ft	
ambient temperature [°F]		
during storage	-22 +149 °F	
during operation	-4 +104 °F	
ambient temperature		
 during storage 	-30 +65 °C	
 during operation 	-20 +40 °C	
Horsepower ratings		
yielded mechanical performance [hp] for 3-phase AC		
motor		
at 200/208 V rated value	0.5 hp	
at 220/230 V rated value	0.75 hp	
at 460/480 V rated value	1.5 hp	
at 575/600 V rated value	2 hp	
Contactor		
size of contactor	NEMA controller size 1	
number of NO contacts for main contacts	3	
operational current at AC at 600 V rated value	27 A	
mechanical service life (switching cycles) of the main contacts typical	10000000	
Auxiliary contact		
number of NC contacts at contactor for auxiliary contacts	0	
number of NO contacts at contactor for auxiliary contacts	1	
number of total auxiliary contacts maximum	8	
contact rating of auxiliary contacts of contactor according to UL	10A@600VAC (A600), 5A@600VDC (P600)	
Coil		
type of voltage of the control supply voltage	AC	
control supply voltage		
 at AC at 50 Hz rated value 	380 440 V	
 at AC at 60 Hz rated value 	440 480 V	
holding power at AC minimum	8.6 W	
apparent pick-up power of magnet coil at AC	218 VA	

annount halding navier of annual at 1, 1, 4, 0	25.1/4
apparent holding power of magnet coil at AC	25 VA
operating range factor control supply voltage rated value of magnet coil	0.85 1.1
percental drop-out voltage of magnet coil related to the input voltage	50 %
ON-delay time	19 29 ms
OFF-delay time	10 24 ms
Overload relay	
product function	
overload protection	Yes
phase failure detection	Yes
asymmetry detection	Yes
ground fault detection	Yes
test function	Yes
external reset	Yes
reset function	Manual, automatic and remote
trip class	CLASS 5 / 10 / 20 (factory set) / 30
adjustable current response value current of the current- dependent overload release	0.75 3.4 A
make time with automatic start after power failure maximum	3 s
relative repeat accuracy	1 %
product feature protective coating on printed-circuit board	Yes
number of NC contacts of auxiliary contacts of overload relay	1
number of NO contacts of auxiliary contacts of overload relay	1
operational current of auxiliary contacts of overload relay	
• at AC at 600 V	5 A
• at DC at 250 V	1 A
contact rating of auxiliary contacts of overload relay according to UL	5A@600VAC (B600), 1A@250VDC (R300)
insulation voltage (Ui)	
with single-phase operation at AC rated value	600 V
with multi-phase operation at AC rated value	300 V
Disconnect Switch	
response value of switch disconnector	30A / 600V
design of fuse holder	non-fusible
operating class of the fuse link	non-fusible
Enclosure	
degree of protection NEMA rating	4, 12
design of the housing	Extra-wide
design of the housing	dustproof, waterproof & weatherproof
Mounting/wiring	
mounting position	vertical
fastening method	Surface mounting and installation
type of electrical connection for supply voltage line-side	Box lug
tightening torque [lbf-in] for supply	35 35 lbf·in
type of connectable conductor cross-sections at line-side	1x (14 2 AWG)
at AWG cables single or multi-stranded temperature of the conductor for supply maximum permissible	75 °C
material of the conductor for supply	AL or CU
type of electrical connection for load-side outgoing feeder	Screw-type terminals
tightening torque [lbf-in] for load-side outgoing feeder	20 24 lbf-in
type of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi-stranded	2x (14 10 AWG)
temperature of the conductor for load-side outgoing feeder maximum permissible	75 °C
material of the conductor for load-side outgoing feeder	CU
type of electrical connection of magnet coil	Screw-type terminals

tightening torque [lbf·in] at magnet coil	5 12 lbf·in
type of connectable conductor cross-sections of magnet coil at AWG cables single or multi-stranded	2x (16 12 AWG)
temperature of the conductor at magnet coil maximum permissible	75 °C
material of the conductor at magnet coil	CU
type of electrical connection for auxiliary contacts	Screw-type terminals
tightening torque [lbf·in] at contactor for auxiliary contacts	10 15 lbf·in
type of connectable conductor cross-sections at contactor at AWG cables for auxiliary contacts single or multi- stranded	1x (12 AWG), 2x (16 14 AWG), 2x (18 16 AWG)
temperature of the conductor at contactor for auxiliary contacts maximum permissible	75 °C
material of the conductor at contactor for auxiliary contacts	CU
type of electrical connection at overload relay for auxiliary contacts	Screw-type terminals
tightening torque [lbf·in] at overload relay for auxiliary contacts	7 10 lbf·in
type of connectable conductor cross-sections at overload relay at AWG cables for auxiliary contacts single or multi-stranded	2x (20 14 AWG)
temperature of the conductor at overload relay for auxiliary contacts maximum permissible	75 °C
material of the conductor at overload relay for auxiliary contacts	CU
Short-circuit current rating	
design of the fuse link for short-circuit protection of the main circuit required	10kA@600V (Class H or K); 100kA@600V (Class R or J)
certificate of suitability	NEMA ICS 2; UL 508; CSA 22.2, No.14
Further information	

Industrial Controls - Product Overview (Catalogs, Brochures,...)

www.usa.siemens.com/iccatalog

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:17DUB82NH


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/US/en/ps/US2:17DUB82NH

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax de.aspx?mlfb=US2:17DUB82NH&lang=en

Certificates/approvals

https://support.industry.siemens.com/cs/US/en/ps/US2:17DUB82NH/certificate



D68782001

last modified: 1/25/2022 🖸