SIEMENS

Data sheet

US2:87IUH6MJ



Pump control panel, Size 3 1/2, Three phase full voltage, Solid-state overload relay, OLR amp range 50-200A, 24VAC 50-60Hz coil, Standard type contactor, 125A circuit breaker, HOA Sel Sw. <(>&<)> Start P.B., Enclosure NEMA type 3/3R, Weather proof outdoor use

-						÷.
E		111	- 0	51	Im	ilar
	9	0.1	~	2		1104

product brand name	Class 87		
design of the product	Pump control panel with MCP		
special product feature	Half-size controller; ESP200 overload relay		
General technical data			
weight [lb]	81 lb		
Height x Width x Depth [in]	41 × 24 × 8 in		
touch protection against electrical shock	NA for enclosed products		
installation altitude [ft] at height above sea level maximum	6560 ft		
ambient temperature [°F]			
 during storage 	-22 +149 °F		
during operation	-4 +104 °F		
ambient temperature			
 during storage 	-30 +65 °C		
during operation	-20 +40 °C		
country of origin	USA		
Horsepower ratings	_		
yielded mechanical performance [hp] for 3-phase AC motor			
• at 200/208 V rated value	30 hp		
 at 220/230 V rated value 	40 hp		
 at 460/480 V rated value 	75 hp		
• at 575/600 V rated value	75 hp		
Contactor			
size of contactor	Controller half size 3 1/2		
number of NO contacts for main contacts	3		
operating voltage for main current circuit at AC at 60 Hz maximum	600 V		
operational current at AC at 600 V rated value	115 A		
mechanical service life (switching cycles) of the main contacts typical	500000		
Auxiliary contact			
number of NC contacts at contactor for auxiliary contacts	0		
number of NO contacts at contactor for auxiliary contacts	1		
number of total auxiliary contacts maximum	7		
contact rating of auxiliary contacts of contactor according to UL	10A@600VAC (A600), 5A@600VDC (P600)		
Coil			
type of voltage of the control supply voltage	AC		
control supply voltage			

	0 0)/			
at DC rated value	00V			
at AC at 50 Hz rated value	24 24 V			
• at AC at 60 Hz rated value	24 24 V 14 W			
holding power at AC minimum				
apparent pick-up power of magnet coil at AC	310 VA			
apparent holding power of magnet coil at AC	26 VA			
operating range factor control supply voltage rated value of magnet coil	0.85 1.1			
percental drop-out voltage of magnet coil related to the input voltage	50 %			
ON-delay time	26 41 ms			
OFF-delay time	14 19 ms			
Overload relay				
product function				
 overload protection 	Yes			
 phase failure detection 	Yes			
 asymmetry detection 	Yes			
 ground fault detection 	Yes			
test function	Yes			
external reset	Yes			
reset function	Manual, automatic and remote			
trip class	CLASS 5 / 10 (factory set) / 20 / 30			
adjustable current response value current of the current- dependent overload release	50 200 A			
tripping time at phase-loss maximum	3 s			
relative repeat accuracy	1 %			
product feature protective coating on printed-circuit board	Yes			
number of NC contacts of auxiliary contacts of overload relay	1			
number of NO contacts of auxiliary contacts of overload relay	1			
operational current of auxiliary contacts of overload relay				
• at AC at 600 V	5 A			
• at DC at 250 V	1 A			
contact rating of auxiliary contacts of overload relay according to UL	5A@600VAC (B600), 1A@250VDC (R300)			
insulation voltage (Ui)				
 with single-phase operation at AC rated value 	600 V			
 with multi-phase operation at AC rated value 	300 V			
Enclosure				
degree of protection NEMA rating of the enclosure	NEMA Type 3R			
design of the housing	Weather proof for outdoor use			
Standard Control Devices				
product component Hand-Off-Auto selector switch	Yes			
type of Hand-Off-Auto selector switch	30mm metal housing with matte finish			
product component start push button	Yes			
type of start push button	30mm metal housing with matte finish			
Circuit Breaker				
type of the motor protection	Motor circuit protector (magnetic trip only)			
operational current of motor circuit breaker rated value	125 A			
adjustable current response value current of instantaneous short-circuit trip unit	500 1250 A			
Mounting/wiring				
mounting position	Vertical			
fastening method	Surface mounting and installation			
type of electrical connection for supply voltage line-side	Box lug			
type of connectable conductor cross-sections at line-side	1x (10 AWG 1/0 AWG)			
at AWG cables single or multi-stranded				
temperature of the conductor for supply maximum permissible	75 °C			
material of the conductor for supply	AL or CU			
type of electrical connection for load-side outgoing feeder	Box lug			

tightening torque [lbf-in] for load-side outgoing feeder	120 120 lbf·in			
type of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi- stranded	1x (14 2/0 AWG)			
temperature of the conductor for load-side outgoing feeder maximum permissible	75 °C			
material of the conductor for load-side outgoing feeder	AL or CU			
type of electrical connection of magnet coil	Screw-type terminals			
tightening torque [lbf·in] at magnet coil	5 12 lbf·in			
type of connectable conductor cross-sections of magnet coil at AWG cables single or multi-stranded	2x (16 12 AWG)			
temperature of the conductor at magnet coil maximum permissible	75 °C			
material of the conductor at magnet coil	CU			
type of electrical connection at contactor for auxiliary contacts	Screw-type terminals			
tightening torque [lbf·in] at contactor for auxiliary contacts	10 15 lbf·in			
type of connectable conductor cross-sections at contactor at AWG cables for auxiliary contacts single or multi- stranded	1x (12 AWG), 2x (16 14 AWG), 2x (18 16 AWG)			
temperature of the conductor at contactor for auxiliary contacts maximum permissible	75 °C			
material of the conductor at contactor for auxiliary contacts	CU			
type of electrical connection at overload relay for auxiliary contacts	Screw-type terminals			
tightening torque [lbf·in] at overload relay for auxiliary contacts	7 10 lbf·in			
type of connectable conductor cross-sections at overload relay at AWG cables for auxiliary contacts single or multi- stranded	2x (20 14 AWG)			
temperature of the conductor at overload relay for auxiliary contacts maximum permissible	75 °C			
material of the conductor at overload relay for auxiliary contacts	CU			
Short-circuit current rating				
design of the short-circuit trip	Instantaneous trip circuit breaker			
breaking capacity maximum short-circuit current (Icu)				
• at 240 V	100 kA			
● at 480 V	100 kA			
• at 600 V	25 kA			
certificate of suitability	NEMA ICS 2; UL 508			
Further information				
Industrial Controls - Product Overview (Catalogs, Brochures,) www.usa.siemens.com/iccatalog				
Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:87IUH6MJ				
Service&Support (Manuals, Certificates, Characteristics, FAQs,)				
https://support.industry.siemens.com/cs/US/en/ps/US2:87IUH6MJ Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros,)				
http://www.automation.siemens.com/bilddb/cax_de.aspx?mlf				
Certificates/approvals https://support.industry.siemens.com/cs/US/en/ps/US2:87IU	H6M.I/certificate			

https://support.industry.siemens.com/cs/US/en/ps/US2:87IUH6MJ/certificate

last modified:

1/8/2022 🖸