



■ 技术参数 SPECIFICATIONS:

- ◆ 线数: 2~12
- ◆ Poles: 2~12
- ◆ 适用线规: AWG #28~#22
- ◆ Applicable Wire: AWG #28~#22
- ◆ 额定电压: 250V DC/AC
- ◆ Voltage Rating: 250V DC/AC
- ◆ 额定电流: 3.0A
- ◆ Current Rating: 3.0A
- ◆ 耐压: 1000V AC
- ◆ Withstand Voltage: 1000V AC
- ◆ 温度范围: -25°C ~ +85°C
- ◆ Working Temperature: -25°C ~ +85°C
- ◆ 绝缘电阻: ≥1000MΩ
- ◆ Insulation Resistance: 1000MΩ (MIN)
- ◆ 接触电阻: ≤10mΩ
- ◆ Contact Resistance: 10mΩ (MAX)
- ◆ 材质/颜色: 尼龙66 UL 94V-0 本色
- ◆ Material: Nylon66 UL 94V-0 Color Nature
- ◆ 包装数量: 1000 Pcs
- ◆ Packaging Quantity: 1000 pcs

15	35.0	38.2	35.0
14	32.5	35.7	32.5
13	30.0	33.2	30.0
12	27.5	30.7	27.5
11	25.0	28.2	25.0
10	22.5	25.7	22.5
9	20.0	23.2	20.0
8	17.5	20.7	17.5
7	15.0	18.2	15.0
6	12.5	15.7	12.5
5	10.0	13.2	10.0
4	7.5	10.7	7.5
3	5.0	8.2	5.0
2	2.5	5.7	2.5
Circuits	Dim.A	Dim.B	Dim.C

APPROVALS		DATE	TITLE:	
DRAWN	G.M.Chen	2015/7/17	EDELON 德之隆® ELECTRONICS CO.,LTD	
CHECKED			TITLE: 2.54mm Crimp Style Connectors	
APPROVALS			PART NO.	A2501-XXP
TOLERANCES ARE		30~0.15 ±	±0.30	ANGLE
		10~0.30 ±	±0.20	UNIT: mm
		5~0.10 ±	±0.15	SCALE: 1:1
		~5	±0.10	DRAWING NO.
			±2'	PROJ.
ECN NO.	REV.	DATE.	DESCRIPTION.	NEW
A				