

■ Features

- Molding Inductor.
- Low Profile,Low Temp.
- Large Current(Over 15A).
- Customize For Different Need.
- Operating temperature:-40°C ~ +125°C.

■ Applications

- General Electronic.
- Video Device,TV,TFT.
- Power Module for PC.
- NB/Lap Top Computer.
- Server,VGA Card/Module.

■ Product Identification

YSMC □□□□□ – □□□ □

(1) (2) (3) (4)


(1) : Type

(2) : Dimensions

(3) : Inductance value

(4) : Inductance Tolerance : N=±30%,M=±20%

■ Shapes and Dimensions (Unit: mm)




| TYPE | A | B | C Max. | D | E | G Ref. | H Ref. | I Ref. |
|-----------|---------|---------|--------|---------|--------------|--------|--------|--------|
| YSMC0420V | 4.0±0.3 | 4.0±0.3 | 2.0 | 4.0±0.3 | 1.2+0.3/-0.2 | 1.5 | 4.3 | 1.5 |

■ YSMC0420V Series

| Part Number | Inductance (uH) @100KHz | DC Resistance (mΩ) | | Heat Rating Current (A) | Saturation Current (A) |
|----------------|----------------------------|--------------------|-------|----------------------------|---------------------------|
| | | Typ. | Max. | | |
| YSMC0420V-1R0M | 1.0±20% | 7.7 | 8.9 | 14.0 | 11.0 |
| YSMC0420V-1R5M | 1.5±20% | 16.0 | 20.0 | 6.0 | 10.0 |
| YSMC0420V-2R2M | 2.2±20% | 27.0 | 34.0 | 5.0 | 8.0 |
| YSMC0420V-3R3M | 3.3±20% | 36.0 | 43.0 | 4.5 | 6.0 |
| YSMC0420V-4R7M | 4.7±20% | 52.0 | 63.0 | 4.0 | 5.5 |
| YSMC0420V-100M | 10±20% | 110.0 | 125.0 | 2.6 | 4.0 |
| YSMC0420V-220M | 22±20% | 258.0 | 280.0 | 1.7 | 2.8 |


- ※ The saturation current value is the DC current value having inductance decrease down to 30%.(at 20°C)
- ※ The temperature rise current value is the DC current value having temperature increase up to 40°C. (at 20°C)
- ※ The rated current is the DC current value that satisfies both of current value saturation current value and temperature rise current value.

■ Taping Dimensions(Unit:mm)




| TYPE | W | A | B | C | D | E | P | K Ref | T | MPQ |
|-----------|--------|---------|----------|------|---------|---------|-------|----------|-----------|------|
| YSMC0420V | 12±0.3 | 4.3±0.1 | 5.10±0.1 | 4.75 | 5.5±0.1 | 2.1±0.1 | 8±0.1 | 2.2 | 0.30±0.05 | 3000 |

■ Reel Dimensions(Unit:mm)




| TYPE | W | W1 | W2 | W3 | A | B | C | D |
|-----------|---------|-----------|---------|---------|-----------|-----------|----------|---------|
| YSMC0420V | 330±2.0 | 12.4±1.50 | 18.4MAX | 11.9Min | 13.0±0.50 | 21.0±0.80 | 2.0±0.50 | 100 Min |

■ Direction of rolling



■ Cover tape peel off condition



Cover tape peel force shall be 0.1N to 1.3N.

Reference peel speed $300 \pm 10 \text{mm/min.}$