#### **FPC/FFC Connector**


# **MINIFLEX® 5-BFN II**

Robust design with hold-down feature, low profile (height = 1.0 mm), 0.5 mm pitch, horizontal, backflip


Product Specifications:		cifications:	Short Actuator	Long Actuator	Applicable FPC/FFC:	
	Board Pitch (mm)		0.5		FPC/FFC Contact Pitch	0.5
	Wiping Length (mm)		1		FPC/FFC Contact Point	Top and Bottom
	Size (mm)	Height	1.0 +/- 0.1		FPC/FFC Thickness (mm)	0.3 +/- 0.05
		Width	Formula: 1.7+(0.5*?p)			
		Depth	Open: 3			
			Close: 3.5	Close: 4.0		
	Pin counts	Range	4-30 (even)	32-60 (even)		
Pin		Available	4, 6, 8, 10, 12, 14, 16,			
			18, 20, 22, 24, 26, 28,	32, 34, 40, 50, 54		
			30			

\* Please inquire for pin counts not listed or outside of the pin count range.

#### Designed to prevent contact distortion



#### Unique actuator holder design prevents actuator drop-off




## Actuator will not fall-off even at $100\ N$ force

\*Housing destruction occurs first \*Force applied from 30 degrees backwards

#### Usability for closing actuator without FPC

The connector will still function even if the actuator is accidentally closed without the FPC being inserted after the SMT process

Connector will still function reliably (contact gap graph 22 pins before and after operating actuator without FPC inserted)




- Insertion force of connector goes up
- Retention force of connector does not change significantly




## **Component Parts Details**


#### **Connector Assembly**



NOTES 1. CONTACT TAIL IS PROJECTION FROM HOUSING IN THE + DIRECTION. (0~0.06) Rev.8




## **Plug Housing Assembly**



I-PEX

ITEMS	SPECIFICATION		
RATING VOLTAGE	50V AC (PER CONTACT)		
RATING AMPERAGE	0.5A DC (PER CONTACT) 7.0A DC (PER CONNECTOR)		
OPERATING TEMPERATURE	233~398K(-40°C~125°C)		
OPERATING HUMIDITY	80% MAX.(NON-CONDENSING)		
CONTACT RESISTANCE	INITIAL : 40mohm MAX. / AFTER TEST : 20mohm MAX.		
INSULATION RESISTANCE	100Mohm MIN.		
DIELECTRIC WITHSTANDING VOLTAGE	AC200V 1min		
DURABILITY	20TH CYCLES		
ACTUATOR LOCKING FORCE (INITIAL / 20TH CYCLES)	INITIAL / 20TH CYCLES : 0.6N(61gf) × n MAX.		
ACTUATOR UNLOCKING FORCE (INITIAL / 20TH CYCLES)	INITIAL / 20TH CYCLES : 0.05N (5gf) × n MIN.		
FPC RETENTION FORCE (INITIAL / AFTER TEST)	INITIAL / AFTER TEST : 0.15N (15gf) × n MIN.		
COPLANARITY	0.08 MAX.		
PRODUCT SPECIFICATION	PRS-1619		
TEST REPORT	TR-12124		
PACKING STANDARD	300-963		
INSTRUCTION MANUAL	HIM-12019		
APPEARANCE CRITERIA No.	QLS-A***		


※ "n" IS THE NUMBER OF PIN




Recommended P/N 20586-0\*\*E-01

Rev.8






Rev.8



CONNECTOR ON RECOMMENDED FOOTPRINT PATTERN



I-PEX

ITEMS	SPECIFICATION		
RATING VOLTAGE	50V AC (PER CONTACT PIN)		
RATING AMPERAGE	0.5A DC (PER CONTACT PIN) 7.0A DC (PER CONNECTOR)		
OPERATING TEMPERATURE	233~398K(-40°C~125°C)		
OPERATING HUMIDITY	80% MAX.(NON-CONDENSING)		
CONTACT RESISTANCE	INITIAL : 40mohm MAX. / AFTER TEST : ⊿20mohm MAX.		
INSULATION RESISTANCE	100Mohm MIN.		
DIELECTRIC WITHSTANDING VOLTAGE	AC200V 1min		
DURABILITY	20TH CYCLES		
ACTUATOR LOCKING FORCE (INITIAL / 20TH CYCLES)	INITIAL / 20TH CYCLES : 0.43N (44gf) × n MAX.		
ACTUATOR UNLOCKING FORCE (INITIAL / 20TH CYCLES)	INITIAL / 20TH CYCLES : 0.025N (2.5gf) × n MIN.		
FPC RETENTION FORCE (INITIAL / AFTER TEST)	INITIAL / AFTER TEST : 0.15N(15gf) × n MIN.		
COPLANARITY	0.08 MAX.		
PRODUCT SPECIFICATION	PRS-2056		
TEST REPORT	TR-15070		
PACKING STANDARD	PST-13064		
INSTRUCTION MANUAL	HIM-12019		
APPEARANCE CRITERIA No.	QLS-A***		

※ "n" IS THE NUMBER OF PIN





I-PEX, MHF, CABLINE, NOVASTACK, EVAFLEX, MINIFLEX, ISH, IARPB, IASLP, ESTORQ, ISFIT, i-Fit and ZenShield are registered trademarks of I-PEX Inc. Please note that the contents in the catalog might be changed without prior notification. I-PEX Inc. assumes no responsibility for any inaccuracies or obligation to update Information on these documents. Please be sure to read and understand the latest "Precautions for Use" and "Instruction Manual" before you use our products. We shall not be responsible for any defects, damages or troubles in case you use our products without following the precautions for use. Please feel free to contact our sales representatives when you use our products for any applications that require very high reliability and safety, or that relate to human life (ex. nuclear power control, aerospace, transportation, medical equipment, safety equipment etc.).

> Contact your sales representative or more detailed information.

www.i-pex.com



