



REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	BATCH PRODUCTION INITIAL RELEASE.	2017.08.16	郭丙建



Specifications  
 Current Rating:1.0Amp  
 Insulation Resistance:1000MΩMin.  
 Dielectric Withstanding Voltage:300VAC  
 Contact Resistance:20mΩMax.  
 Operating Temperature:-40°C to +105°C  
 Materials  
 Contact Material:Phosphor Bronze  
 Insulator Material:High Temperature Thermoplastic, UL 94V-0 LCP or the equivalent material  
 All materials must meet Greenconn hazardous substances control standards.

Recommended P.C.Board Layout  
 (Tolerance:±0.05)



### Ordering Information

C SEC203 - XX XX B 011 C 1 A X

No. of Pins per Row  
03~40

Standard Plating  
02=Gold Flash  
Selective Plating  
01=Tin  
05=Gold Flash/Tin

Color  
1=Black

Standard Packing  
C=Tube(03~40PIN)  
Selective Packing  
E=Cap+Tube(04~40PIN)  
F=Cap+Tape&Reel  
G=Acetate tape+Tube  
H=Acetate tape+T&R

格稜股份有限公司  
**Greenconn Corporation**

#### GENERAL TOLERANCE

X.*±5.0°	X.±0.30
.X*±3.0°	.X±0.25
.XX*±2.0°	.XX±0.15
.XXX*±1.0°	.XXX±0.10

DESIGNED: 郭丙建 DATE: 2017.08.16

CHECKED: 林煌隆 DATE: 2017.08.16

CO SIGNED: 劉北平 DATE: 2017.08.16

APPROVED: 陳義昌 DATE: 2017.08.16

DWG. NO.

CSEC203-CB11CA

PART NO.

CSEC203-XXXX B011R1AX

TITLE.

1.27 FEMALE HEADER  
 DUAL ROWS SMT TYPE  
 W/POST

REV.	UNIT.	SCALE.	PAGE.
01	mm	5:1	1/1