3RA2110-1CA15-1AP0

Data sheet



Load feeder fuseless, Direct-on-line starting 400 V AC, Size S00 1.80...2.50 A 230 V AC screw terminal for installation on standard mounting rail (also fulfills type of coordination 1) Type of coordination 2, Iq = 150 kA 1 NO (contactor)

product brand name	SIRIUS
product designation	Direct (on-line) starter
design of the product	for standard rail or screw mounting
product type designation	3RA21
manufacturer's article number	
 of the supplied contactor 	3RT2015-1AP01
 of the supplied circuit-breakers 	3RV2011-1CA10
 of the supplied link module 	3RA1921-1DA00
General technical data	
size of the circuit-breaker	S00
size of load feeder	S00
insulation voltage with degree of pollution 3 at AC rated value	690 V
surge voltage resistance rated value	6 kV
degree of protection NEMA rating	other
shock resistance according to IEC 60068-2-27	6g / 11 ms
mechanical service life (switching cycles) of contactor typical	30 000 000
type of assignment	2
type of protection according to ATEX directive 2014/34/EU	Ex II (2) GD
certificate of suitability according to ATEX directive 2014/34/EU	DMT 02 ATEX F 001
Substance Prohibitance (Date)	10/01/2009
Ambient conditions	
ambient temperature	
 during operation 	-20 +60 °C
during storage	-50 +80 °C
 during transport 	-50 +80 °C
temperature compensation	-20 +60 °C
relative humidity during operation	10 95 %
Main circuit	
number of poles for main current circuit	3
design of the switching contact	electromechanical
adjustable current response value current of the current-dependent overload release	1.8 2.5 A
operating voltage	
• rated value	690 V
at AC-3 rated value maximum	690 V
operating frequency rated value	50 60 Hz

operational current at AC-3 at 400 V rated value	1.9 A
operating power at AC-3	
 at 400 V rated value 	750 W
Control circuit/ Control	
type of voltage of the control supply voltage	AC
control supply voltage at AC	
 at 50 Hz rated value 	230 V
at 50 Hz rated value	230 230 V
at 60 Hz rated value	230 V
at 60 Hz rated value	230 230 V
apparent holding power of magnet coil at AC	4.2 VA
Auxiliary circuit	
product extension auxiliary switch	Yes
Protective and monitoring functions	
trip class	CLASS 10
design of the overload release	thermal (bimetallic)
UL/CSA ratings	
full-load current (FLA) for 3-phase AC motor	
at 480 V rated value	2.5 A
yielded mechanical performance [hp]	2.0 N
for 3-phase AC motor	
— at 200/208 V rated value	0.5 hp
— at 220/230 V rated value	0.5 hp
— at 460/480 V rated value	1 hp
— at 450/460 V rated value	1.5 hp
	1.5 Hp
Short-circuit protection	Vac
product function short circuit protection	Yes
design of the short-circuit trip	magnetic
conditional short-circuit current (Iq)	150,000 A
at 400 V according to IEC 60947-4-1 rated value	150 000 A
Installation/ mounting/ dimensions	
mounting position	vertical
fastening method	screw and snap-on mounting onto 35 mm standard mounting rail
height	167 mm
width	45 mm
depth	97 mm
required spacing	
for grounded parts forwards	20 mm
— forwards — backwards	20 mm
	0 mm 50 mm
— upwards — at the side	50 mm
— at the side — downwards	10 mm
downwards for live parts	IV IIIIII
for live parts — forwards	20 mm
— forwards — backwards	20 mm 0 mm
— packwards — upwards	50 mm
— upwards — downwards	10 mm
— downwards — at the side	20 mm
	ZV IIIII
Connections/ Terminals	
type of electrical connection	corous tuno terminale
for main current circuit for qualifory and control circuit	screw-type terminals
for auxiliary and control circuit	screw-type terminals
Safety related data	
B10 value with high demand rate according to SN 31920	1 000 000
proportion of dangerous failures	70 0/
with high demand rate according to SN 31920	73 %
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front
Communication/ Protocol	

protocol is supported • PROFINET IO protocol • PROFIsafe protocol • PROFIsafe protocol protocol is supported AS-Interface protocol No

Certificates/ approvals

General Product Approval

For use in hazardous locations Declaration of Conformity



Confirmation



EAC





Declaration of Conformity

Test Certificates

Marine / Shipping



Type Test Certificates/Test Report

Special Test Certificate





Confirmation



Vibration and Shock

Marine / Shipping

other Railway









Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2110-1CA15-1AP0

Cax online generator

 $\underline{http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en\&mlfb=3RA2110-1CA15-1APO}$

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RA2110-1CA15-1AP0

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA2110-1CA15-1AP0&lang=en

Characteristic: Tripping characteristics, I2t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RA2110-1CA15-1AP0/char

Further characteristics (e.g. electrical endurance, switching frequency)

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2110-1CA15-1AP0&objecttype=14&gridview=view1

last modified:

2/16/2022

