SIEMENS

Data sheet


3RA2210-1CA15-2AK6



FUSELESS LOAD FEEDER REVERSING OPERATION, AC 400V, S00 1.8...2.5A, AC 110/120V 50/60HZ SCREW TERMINAL FOR RAIL MOUNTING, TYPE OF ASSIGNMENT 2,IQ = 150KA (ALSO FULFILLS TYPE OF ASSIGNMENT 1) 1NC (CONTACTOR)

product brand name	SIRIUS
product designation	non-fused load feeders 3RA2
design of the product manufacturer's article number	reversing starter
of the supplied contactor	2072015 14//62
	<u>3RT2015-1AK62</u>
of the supplied circuit-breakers	<u>3RV2011-1CA10</u>
of the supplied link module <u>3RA1921-1DA00</u>	
General technical data	
size of the circuit-breaker	S00
size of load feeder	S00
product extension auxiliary switch	Yes
insulation voltage with degree of pollution 3 at AC rated value	690 V
degree of pollution	3
surge voltage resistance rated value	6 kV
shock resistance according to IEC 60068-2-27	6g / 11 ms
mechanical service life (switching cycles) of contactor typical	30 000 000
type of assignment	2
Substance Prohibitance (Date)	10/01/2009
Ambient conditions	
ambient temperature	
 during operation 	-20 +60 °C
 during storage 	-50 +80 °C
 during transport 	-50 +80 °C
Main circuit	
number of poles for main current circuit	3
design of the switching contact	electromechanical
adjustable current response value current of the current-dependent overload release	1.8 2.5 A
operating voltage	
rated value	690 V
 at AC-3 rated value maximum 	690 V
operating frequency rated value	50 60 Hz
operational current at AC-3 at 400 V rated value	1.9 A
operating power at AC-3	
at 400 V rated value	750 W
• at 500 V rated value	1 100 W
• at 690 V rated value	1 100 W
Control circuit/ Control	

control supply voltage at AC	440.14
at 50 Hz rated value	110 V
at 60 Hz rated value	120 V
apparent holding power of magnet coil at AC	4.2 VA
Protective and monitoring functions	
trip class	CLASS 10
design of the overload release	thermal (bimetallic)
response value current of instantaneous short-circuit trip unit	32.5 A
UL/CSA ratings	
full-load current (FLA) for 3-phase AC motor	
at 480 V rated value	2.15 A
at 600 V rated value	2.24 A
yielded mechanical performance [hp]	
• for single-phase AC motor	
— at 230 V rated value	0.17 hp
• for 3-phase AC motor	····
— at 200/208 V rated value	0.5 hp
— at 220/230 V rated value	0.5 hp
— at 460/480 V rated value	1 hp
— at 575/600 V rated value	1.5 hp
Short-circuit protection	
product function short circuit protection	Yes
design of the short-circuit trip	magnetic
conditional short-circuit current (lq)	
 at 690 V according to IEC 60947-4-1 rated value 	10 000 A
• at 400 V according to IEC 60947-4-1 rated value	153 000 A
• at 500 V according to IEC 60947-4-1 rated value	100 000 A
Installation/ mounting/ dimensions	
mounting position	vertical
fastening method	screw and snap-on mounting onto 35 mm standard mounting rail
height	
width	90 mm
depth	97.1 mm
required spacing	
 for grounded parts 	
— forwards	0 mm
— backwards	0 mm
— upwards	20 mm
— at the side	9 mm
— downwards	10 mm
 for live parts 	
— forwards	0 mm
— backwards	0 mm
— upwards	20 mm
— downwards	10 mm
— downwards — at the side	
	10 mm
— at the side Connections/ Terminals	10 mm 9 mm
- at the side Connections/ Terminals type of electrical connection for main current circuit	10 mm
— at the side Connections/ Terminals	10 mm 9 mm screw-type terminals
	10 mm 9 mm screw-type terminals 0.5 4 mm ² , 2x (0.75 2.5 mm ²)
	10 mm 9 mm screw-type terminals
 at the side Connections/ Terminals type of electrical connection for main current circuit type of connectable conductor cross-sections for main contacts stranded at AWG cables for main contacts connectable conductor cross-section for main contacts finely stranded with core end processing 	10 mm 9 mm screw-type terminals 0.5 4 mm ² , 2x (0.75 2.5 mm ²) 2x (20 16), only for contactor 2x (18 14), 2x 12
 at the side Connections/ Terminals type of electrical connection for main current circuit type of connectable conductor cross-sections for main contacts stranded at AWG cables for main contacts connectable conductor cross-section for main contacts finely stranded with core end processing Safety related data 	10 mm 9 mm screw-type terminals 0.5 4 mm ² , 2x (0.75 2.5 mm ²) 2x (20 16), only for contactor 2x (18 14), 2x 12 0.5 2.5 mm ²
 at the side Connections/ Terminals type of electrical connection for main current circuit type of connectable conductor cross-sections for main contacts stranded at AWG cables for main contacts connectable conductor cross-section for main contacts finely stranded with core end processing Safety related data B10 value with high demand rate according to SN 31920 proportion of dangerous failures with high demand rate 	10 mm 9 mm screw-type terminals 0.5 4 mm ² , 2x (0.75 2.5 mm ²) 2x (20 16), only for contactor 2x (18 14), 2x 12
 at the side Connections/ Terminals type of electrical connection for main current circuit type of connectable conductor cross-sections for main contacts stranded at AWG cables for main contacts connectable conductor cross-section for main contacts finely stranded with core end processing Safety related data B10 value with high demand rate according to SN 31920 	10 mm 9 mm screw-type terminals 0.5 4 mm ² , 2x (0.75 2.5 mm ²) 2x (20 16), only for contactor 2x (18 14), 2x 12 0.5 2.5 mm ² 1 000 000



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2210-1CA15-2AK6

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA2210-1CA15-2AK6

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RA2210-1CA15-2AK6

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)


http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA2210-1CA15-2AK6&lang=en

Characteristic: Tripping characteristics, I²t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RA2210-1CA15-2AK6/char

Further characteristics (e.g. electrical endurance, switching frequency)

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2210-1CA15-2AK6&objecttype=14&gridview=view1



last modified:

12/15/2020 🖸