


REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	BATCH PRODUCTION INITIAL RELEASE.	2021.08.18	郭康
02	△	Modify the number of pins applicable to the cap(N-N210904)	2021.09.02	郭康



Specifications  
 Current Rating:1.0Amp  
 Insulation Resistance:1000MΩMin.  
 Dielectric Withstanding Voltage:300VAC  
 Contact Resistance:20mΩMax.  
 Operating Temperature:-55°C to +125°C  
 Materials  
 Contact Material:Phosphor Bronze  
 Insulator Material:High Temperature Thermoplastic, UL 94V-0 Nylon (**Halogen Free**) or the equivalent material  
 All materials must meet Greenconn requirement for environment protection.


### Ordering Information

C SEC202 - XX XX A 001 R 1 A X

No. of Pins per Row 02~50  
 Standard Plating 02=Gold Flash  
 Selective Plating 01=Tin 05=Gold Flash/Tin  
 Color 1=Black  
 Standard Packing C=Tube(used 04~50pin)  
 Selective Packing E=Cap+Tube(used 04~50pin)  
 F=Cap+Tape&Reel  
 G=Acetate tape+Tube(used 04~50pin)  
 H=Acetate tape+T&R

DIM.C	NOTE
4mm	03PIN △
5mm	04~50PIN

Recommended P.C.Board Layout  
 (Tolerance:±0.05)



3RD.ANG PROJ.  
 3/1

GENERAL TOLERANCE	
X'±5.0'	X.±0.30
.X'±3.0'	.X±0.25
.XX'±2.0'	.XX±0.15
.XXX'±1.0'	.XXX±0.10

DESIGNED: 郭康  
 CHECKED: 張春進  
 APPROVED: 邱國延

DATE: 2021.09.02  
 DATE: 2021.09.02  
 DATE: 2021.09.02

DWG. NO.  
 CSEC202-CA1RA  
 PART NO.  
 CSEC202-XXXX A001R1AX

TITLE.  
 1.27 FEMALE HEADER  
 DUAL ROWS SMT TYPE  
 BASE 4.40H