






TPA Type, A KEY






TPA Type, B KEY



Standard, C KEY



Standard, D KEY



Specifications:
 规格:
 Voltage rating:400V AC/DC
 额定电压: 400V AC/DC
 Current rating:14A AC/DC
 额定电流: 14A AC/DC
 Withstanding voltage:1800V AC/minute
 耐受电压: 1800V AC/分钟
 Temperature range:-40℃-+105℃
 温度范围: -40℃-+105℃
 Insulation resistance:1000MΩ min
 绝缘电阻: 1000MΩ Min
 Contact resistance:10mΩ Max
 接触电阻: 10mΩ Max

X3501 H - XX X - N0
 ① ② ③ ④ ⑤

- 1.Series No
- 2.Category:H-HSG
- 3.Row No.Pin No:XX-02~12P
- 4.A:TPA Type, A KEY Black
 B:TPA Type, B KEY Nature
 C:Standard, C KEY Black
 D:Standard, D KEY Nature
- 5.Material:N0-Nylon UL94V-0

Poles	Dimensions	
	A	B
02	3.50	8.00
03	7.00	11.50
04	10.50	15.00
05	14.00	18.50
06	17.50	22.00
07	21.00	25.50
08	24.50	29.00
12	38.50	43.00

X3501H-XXX-N0	Nylon	X3501W	X3501T
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

MARK	DESCRIPTION	DATE	REVISED	APPROVED	ANGLAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
					L > 63	±0.5



DSND		SCALE: N/A	MODEL TYPE: 3.5mm Crimp Style Connector
DWN		VIEW:	PART NO.: X3501H-XXX-N0
CHKD		UNIT: mm/in	DWG NO.: X-X3501H-XXX-N0
APPD		SIZE: A4	

XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0