


Data sheet for SINAMICS G120X

Article No.: 6SL3220-2YH44-0UP0

Client order no. : Order no. : Offer no. : Remarks :



Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time

| General tech. specifications | | |
|-----------------------------------|---|--|
| Power factor λ | 0.90 0.95 | |
| Offset factor $\cos \phi$ | 0.99 | |
| Efficiency η | 0.98 | |
| Sound pressure level (1m) | 72 dB | |
| Power loss 3) | 1.820 kW | |
| Filter class (integrated) | Unfiltered | |
| EMC category (with accessories) | without | |
| Safety function "Safe Torque Off" | without SIRIUS device (e.g. via S7- 1500F) | |

| Com | mur | nica | tion |
|-------|-----|------|-------|
| COIII | mu | IICu | CIOII |

Communication PROFIBUS DP



Item no. : Consignment no. : Project :

| Inputs i | outputs | |
|--------------------------------------|------------------------|--|
| Standard digital inputs | | |
| Number | 6 | |
| Switching level: $0 \rightarrow 1$ | 11 V | |
| Switching level: $1 \rightarrow 0$ | 5 V | |
| Max. inrush current | 15 mA | |
| Fail-safe digital inputs | | |
| Number | 1 | |
| Digital outputs | | |
| Number as relay changeover contact | 2 | |
| Output (resistive load) | DC 30 V, 5.0 A | |
| Number as transistor | 0 | |
| Analog / digital inputs | | |
| Number | 2 (Differential input) | |
| Resolution | 10 bit | |
| Switching threshold as digital input | | |
| 0 → 1 | 4 V | |
| 1 → 0 | 1.6 V | |
| Analog outputs | | |

PTC/ KTY interface

Number

1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy $\pm 5\,^{\circ}\text{C}$

1 (Non-isolated output)

| Closed-loop control techniques | |
|---|-----|
| V/f linear / square-law / parameterizable | Yes |
| V/f with flux current control (FCC) | Yes |
| V/f ECO linear / square-law | Yes |
| Sensorless vector control | Yes |
| Vector control, with sensor | No |
| Encoderless torque control | No |
| Torque control, with encoder | No |




Data sheet for SINAMICS G120X

6SL3220-2YH44-0UP0 Article No.:


| Ambient conditions | | |
|--------------------------------|--|--|
| Standard board coating type | Class 3C2, according to IEC 60721-3-3: 2002 | |
| Cooling | Air cooling using an integrated fan | |
| Cooling air requirement | 0.153 m ³ /s (5.403 ft ³ /s) | |
| Installation altitude | 1,000 m (3,280.84 ft) | |
| Ambient temperature | | |
| Operation | -20 45 °C (-4 113 °F) | |
| Transport | -40 70 °C (-40 158 °F) | |
| Storage | -25 55 °C (-13 131 °F) | |
| Relative humidity | | |
| Max. operation | 95 % At 40 °C (104 °F), condensation and icing not permissible | |
| Co | onnections | |
| Signal cable | | |
| Conductor cross-section | 0.15 1.50 mm ² (AWG 24 AWG 16) | |
| Line side | | |
| Version | M10 screw | |
| Conductor cross-section | 35.00 2 x 120.00 mm ² (AWG 1 AWG 2 x 4/0) | |
| Motor end | | |
| Version | M10 screw | |
| Conductor cross-section | 35.00 2 x 120.00 mm ² (AWG 1 AWG 2 x 4/0) | |
| DC link (for braking resistor) | | |
| PE connection | M10 screw | |
| Max. motor cable length | | |
| Shielded | 300 m (984.25 ft) | |
| Unshielded | 450 m (1,476.38 ft) | |
| | | |

| Mechanical data | | |
|---------------------------|---|--|
| Degree of protection | IP20 / UL open type | |
| Frame size | FSF | |
| Net weight | 61 kg (134.48 lb) | |
| Dimensions | | |
| Width | 305 mm (12.01 in) | |
| Height | 709 mm (27.91 in) | |
| Depth | 369 mm (14.53 in) | |
| | | |
| Standards | | |
| Compliance with standards | UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH | |
| CE marking | EMC Directive 2004/108/EC, Low- Voltage Directive 2006/95/EC | |
| | | |



Converter losses to IEC61800-9-2*

IE2



The percentage values show the losses in relation to the rated apparent power of

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*converted values

Efficiency class

¹⁾ The output current and HP ratings are valid for the voltage range 550V-600V

³⁾Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.



Data sheet for SINAMICS G120X

Article No.: 6SL3220-2YH44-0UP0

| | Operator pane | el: Basic Operator Panel (BOP-2) |
|----------------------|---------------------|----------------------------------|
| | Screen | |
| Display design | LCD, monochrome | Ambient temperature |
| | Manhautinal data | Operation |
| | Mechanical data | Storage |
| Degree of protection | IP55 / UL type 12 | Transpart |
| Net weight | 0.140 kg (0.31 lb) | Transport |
| Dimensions | - | Relative humidity at 25 |
| Width | 70.00 mm (2.76 in) | Max. operation |
| Height | 106.85 mm (4.21 in) | |
| Depth | 19.60 mm (0.77 in) | Certificate of suitability |
| | | |

| Ambient conditions | | |
|----------------------------------|--------------------------|--|
| Ambient temperature | | |
| Operation | 0 50 °C (32 122 °F) | |
| Storage | -40 70 °C (-40 158 °F) | |
| Transport | -40 70 °C (-40 158 °F) | |
| Relative humidity at 25°C during | | |
| Max. operation | 95 % | |
| | | |
| Approvals | | |
| Certificate of suitability | CE, cULus, EAC, KCC, RCM | |