

HY951140A

Electrical Specification @25°C

RoHS Compliant (PB Free)

Isolation: 1500Vrms 0.5mA 60sec (UTP Side to Chip Side)

OCL: 350uH Minimum @100KHz 100mV with 8mADC Insertion Loss: -1.1dB Typical @100KHz \sim 100MHz Return Loss: -20dB Minimum @1MHz \sim 10MHz


-16dB Minimum @10MHz ~ 30MHz-12dB Minimum @30MHz ~ 60MHz-10dB Minimum @60MHz ~ 80MHz

Common to Common Mode Rejection: −35dB Typical @30MHz ~ 100MHz

Crosstalk: $-40 \, \text{dB}$ Typical @1MHz $\sim 30 \, \text{MHz}$ $-35 \, \text{dB}$ Typical @30MHz $\sim 60 \, \text{MHz}$

-30dB Typical @60MHz ~ 100 MHz

Schematics



Notes: Connect CHS GND to PCB Ground


REV.: 00 1 of 4



HY951140A

- RoHS Compliant (Pb Free)
- Designed for Network Interface Card Application
- Meets or Exceeds IEEE802.3 standards including 350uH Min OCL with 8mADC
- High performance for EMI suppression, Crosstalk, Return Loss and Consistent Electrical
- Minimum 1500Vrms isolation per IEEE802.3 requirement
- Minimize PCB space and Simplify PCB Layout
- Less magnetic components to place on PCB, Higher reliability and yields
- UL Recognized Component: File # E330599

Mechanical Dimensions:





Dimensions in mm


Unless otherwise specified, Tolerance: .xx ± 0.25

REV.: 00 2 of 4




HY951140A

Mechanical Dimensions:



Recommended PCB layout (Component Side View) All dimension tolerance are ± 0.08 unless otherwise specified

Suggested Panel Cutout:



Dimensions in mm

Unless otherwise specified, Tolerance: .xx ± 0.25

REV.: 00 3 of 4

Address: No.16, Industrial Road Central, Industrial Zone, Xiaolan Town, Zhongshan City, Guangdong Province, China
Tel: (0760)86103511 86103508 Fax: (0760)86103686 Post code: 528416
E-Mail: sales@hanrun.com http://www.hanrun.com

1x1 Port Tab upright RJ45 Connector with Integrated Magnetics



HY951140A

Material Specification:

Housing: PA66 GF Black UL94V-0

Shield: 30u" Nickel over 0.20mm Thickness Brass

Insert: PA66 GF Black UL94V-0

Phosphor Bronze 0.30mm Thickness
Plating Area, 30u" gold over 50u" nickel
Solder Area, 100u" tin over 50u" nickel

Contact pin: PA66 GF Black UL94V-0

Phosphor Bronze; 100u" Tinning

Mechanical Performance:

Contact resistance: 30 $m\Omega$ Maximum

Mating force: 5 lbs Maximum
Unmating force: 5 lbs Maximum
Operating life: 750 Cycles Minimum

Operating and Storage Temperature:

Operating Temperature Range: $0^{\circ}\text{C} \sim +70^{\circ}\text{C}$ Storage Temperature Range: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$

REV.: 00 4 of 4