# SIEMENS

Data sheet for SINAMICS G120X

#### Article No. :

#### 6SL3230-2YE12-0UF0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Rated data		
Input		
Number of phases	3 AC	
Line voltage	380 480 V +10 %	% -20 %
Line frequency	47 63 Hz	
Rated voltage	400V IEC	480V NEC
Rated current (LO)	2.80 A	2.70 A
Rated current (HO)	2.10 A	2.00 A
Output		
Number of phases	3 AC	
Rated voltage	400V IEC	480V NEC <sup>1)</sup>
Rated power (LO)	1.10 kW	1.50 hp
Rated power (HO)	0.75 kW	1.00 hp
Rated current (LO)	3.10 A	3.00 A
Rated current (HO)	2.20 A	2.10 A
Rated current (IN)	3.20 A	
Max. output current	3.40 A	
Pulse frequency	4 kHz	
Output frequency for vector control	0 200 Hz	
Output frequency for V/f control	0 550 Hz	
Over the end over a billion		

#### **Overload capability**

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time

General tech. specifications		
Power factor $\lambda$	0.70 0.85	
Offset factor $\cos \phi$	0.96	
Efficiency η	0.97	
Sound pressure level (1m)	55 dB	
Power loss 3)	0.055 kW	
Filter class (integrated)	Unfiltered	
EMC category (with accessories)	without	
Safety function "Safe Torque Off"	without	
Communication		

Communication

PROFINET, EtherNet/IP

ltem no. : Consignment no. : Project :

Inputs / outputs		
Standard digital inputs		
Number	6	
Switching level: $0 \rightarrow 1$	11 V	
Switching level: $1 \rightarrow 0$	5 V	
Max. inrush current	15 mA	
Fail-safe digital inputs		
Number	1	
Digital outputs		
Number as relay changeover contact	2	
Output (resistive load)	DC 30 V, 5.0 A	
Number as transistor	0	
Analog / digital inputs		
Number	2 (Differential input)	
Resolution	10 bit	
Switching threshold as digital input		
0 → 1	4 V	
1 → 0	1.6 V	
Analog outputs		
Number	1 (Non-isolated output)	
PTC/ KTY interface		
1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy $\pm 5~^\circ\text{C}$		

Closed-loop control techniques		
V/f linear / square-law / parameterizable	Yes	
V/f with flux current control (FCC)	Yes	
V/f ECO linear / square-law	Yes	
Sensorless vector control	Yes	
Vector control, with sensor	No	
Encoderless torque control	No	
Torque control, with encoder	No	

## SIEMENS

#### Data sheet for SINAMICS G120X

#### Article No. :

#### 6SL3230-2YE12-0UF0

Ambio	ent conditions
Standard board coating type	Class 3C3, according to IEC 60721-3-3: 2002
Cooling	Air cooling using an integrated fan
Cooling air requirement	0.005 m³/s (0.177 ft³/s)
Installation altitude	1,000 m (3,280.84 ft)
Ambient temperature	
Operation	-20 45 °C (-4 113 °F)
Transport	-40 70 °C (-40 158 °F)
Storage	-25 55 °C (-13 131 °F)
Relative humidity	
Max. operation	95 % At 40 °C (104 °F), condensation and icing not permissible
Connections	
Signal cable	
Conductor cross-section	0.15 1.50 mm² (AWG 24 AWG 16)
Line side	
Version	screw-type terminal
Conductor cross-section	1.50 2.50 mm <sup>2</sup> (AWG 16 AWG 14)
Motor end	
Version	Screw-type terminals
Conductor cross-section	1.50 2.50 mm² (AWG 16 AWG 14)
DC link (for braking resistor)	
PE connection	On housing with M4 screw
Max. motor cable length	
Shielded	150 m (492.13 ft)
Unshielded	300 m (984.25 ft)

Mec	hanical data	
Degree of protection	IP20 / UL open type	
Frame size	FSA	
Net weight	3.2 kg (7.05 lb)	
Dimensions		
Width	73 mm (2.87 in)	
Height	232 mm (9.13 in)	
Depth	218 mm (8.58 in)	
S	tandards	
Compliance with standards	UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH	
CE marking	EMC Directive 2004/108/EC, Low- Voltage Directive 2006/95/EC	
Converter los	sses to IEC61800-9-2*	
Efficiency class	IE2	
Comparison with the reference converter (90% / 100%)	31.1 %	
I ↓ 42.5 W (2.0 %)	47.1 W (2.2 %) 54.8 W (2.6 %)	
100% •	•	
	37.1 W (1.7 %) 39.9 W (1.9 %)	
35.3 W (1.6 %)		
35.3 W (1.6 %)	••	
50% •	33.1 W (1.5 %)	

The percentage values show the losses in relation to the rated apparent power of the converter.

90% **f** 

50%

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

\*converted values

<sup>1)</sup>The output current and HP ratings are valid for the voltage range 440V-480V

<sup>3)</sup> Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.

### SIEMENS

### Data sheet for SINAMICS G120X

#### Article No. :

#### 6SL3230-2YE12-0UF0

#### Operator panel: Basic Operator Panel (BOP-2)

Screen		
Display design	LCD, monochrome	
Mechanical data		
Degree of protection	IP55 / UL type 12	
Net weight	0.140 kg (0.31 lb)	
Dimensions		
Width	70.00 mm (2.76 in)	
Height	106.85 mm (4.21 in)	
Depth	19.60 mm (0.77 in)	

Ambient conditions		
Ambient temperature		
Operation	0 50 °C (32 122 °F)	
Storage	-40 70 °C (-40 158 °F)	
Transport	-40 70 °C (-40 158 °F)	
Relative humidity at 25°C during		
Max. operation	95 %	
Approvals		
Certificate of suitability	CE, cULus, EAC, KCC, RCM	