

The 33CS/36CS Series inductor family combines exceptionally high Q values only achieved by an airwound coil, with automatic placement capability. The high frequency range capability and durable mechanical stability make this component very attractive for signal conditioning in a wide variety of applications. The 33CS/36CS Series is an airwound coil designed for auto placement and compatibility.


Features

- Inductance Range: 6.8–49.8nH
- Machine autoplacable
- Reflow solderability
- High Q
- Excellent environmental and mechanical characteristics
- Packaged on tape and reel in 2,000 piece quantity

33CS



36CS



Tolerance: ± 0.2
Unit: mm

STANDARD PARTS SELECTION GUIDE

TYPE 33CS

TOKO Part Number	Winding Turns	Inductance nH	Tolerance (%)	Q (min.)	Testing Frequency (MHz min.)	Self Resonant Frequency (MHz min.)	Rated DC Current (mA max.)
Y655LY-01K=P3	1.5	6.8	± 10	70	150	3,000	1,000
Y655LY-02K=P3	2.5	10.5	± 10	75	150	3,000	1,000
Y655LY-03K=P3	3.5	15.3	± 10	75	150	3,000	1,000
Y655LY-04K=P3	4.5	21.6	± 10	75	150	2,500	1,000

TYPE 36CS

656LZ-05K=P3	5.5	22.0	± 10	85	150	2,500	1,000
656LZ-06K=P3	6.5	27.5	± 10	85	150	2,200	1,000
656LZ-07K=P3	7.5	33.1	± 10	85	150	2,000	1,000
656LZ-08K=P3	8.5	41.1	± 10	85	150	2,000	1,000
656LZ-09K=P3	9.5	49.8	± 10	85	150	1,700	1,000

Note: =P3 is added to each part number to indicate tape and reel packaging.