

JCK Series



- 2:1 Input Range
- -40 °C to +100 °C Operating Temperature
- Single & Dual Outputs
- Remote On/Off
- High Efficiency – up to 93%
- 1600 VDC Isolation
- 3 Year Warranty

Specification

Input

Input Voltage Range	<ul style="list-style-type: none"> • 12 V (9-18 VDC) • 24 V (18-36 VDC) • 48 V (36-75 VDC)
Input Current	<ul style="list-style-type: none"> • See table
Undervoltage Lockout	<ul style="list-style-type: none"> • 12 V models: ON 8.6 V, OFF 7.9 V typical • 24 V models: ON 17.8 V, OFF 16 V typical • 48 V models: ON 33.5 V, OFF 30.5 V typical
Input Surge	<ul style="list-style-type: none"> • 12 V models 36 VDC for 100 ms • 24 V models 50 VDC for 100 ms • 48 V models 100 VDC for 100 ms

Output

Output Voltage	<ul style="list-style-type: none"> • See table
Output Voltage Trim	<ul style="list-style-type: none"> • ±10% max on single outputs
Minimum Load	<ul style="list-style-type: none"> • No minimum load required
Line Regulation	<ul style="list-style-type: none"> • ±0.5% max
Load Regulation	<ul style="list-style-type: none"> • Single output models: ±0.5% max • Dual output models: ±1% max balanced outputs
Cross Regulation	<ul style="list-style-type: none"> • ±5% for dual outputs (see note 2)
Setpoint Accuracy	<ul style="list-style-type: none"> • ±1% max
Start Up Delay	<ul style="list-style-type: none"> • <20 ms
Start Up Rise Time	<ul style="list-style-type: none"> • <5 ms
Ripple & Noise	<ul style="list-style-type: none"> • 75 mV pk-pk (see note 3)
Transient Response	<ul style="list-style-type: none"> • ±3% max deviation, recovery to within 1% in 250 μs for a 25% load change
Temperature Coefficient	<ul style="list-style-type: none"> • 0.02%/°C
Overvoltage Protection	<ul style="list-style-type: none"> • 3.3 V models: 3.9 V typical • 5 V models: 6.2 V typical • 12 V models: 15 V typical • 15 V models: 18 V typical • ±12 V models: ±15 V typical • ±15 V models: ±18 V typical
Overload Protection	<ul style="list-style-type: none"> • >140% of full load at nominal input
Short Circuit Protection	<ul style="list-style-type: none"> • Trip & restart (hiccup mode), auto recovery
Remote On/Off	<ul style="list-style-type: none"> • On = Logic High (>3.0 V) or Open • Off = Logic Low (<1.2 V) or short pin 2 to pin 6
Capacitive Load	<ul style="list-style-type: none"> • See table

General

Efficiency	<ul style="list-style-type: none"> • See table
Isolation	<ul style="list-style-type: none"> • 1600 VDC Input to Output • 1600 VDC Input to Case • 1600 VDC Output to Case
Isolation Capacitance	<ul style="list-style-type: none"> • 1200 pF typical
Isolation Resistance	<ul style="list-style-type: none"> • 10⁹Ω min
Switching Frequency	<ul style="list-style-type: none"> • 330 kHz typical
Power Density	<ul style="list-style-type: none"> • 25 W/in³
MTBF	<ul style="list-style-type: none"> • >680 kHrs minimum to MIL-HDBK-217F at 25 °C, GB

Environmental

Operating Temperature	<ul style="list-style-type: none"> • -40 °C to +100 °C, derate from 100% load at +70 °C to 0% load at +100 °C
Case Temperature	<ul style="list-style-type: none"> • +100 °C max
Cooling	<ul style="list-style-type: none"> • Convection-cooled
Operating Humidity	<ul style="list-style-type: none"> • Up to 95% RH, non-condensing
Storage Temperature	<ul style="list-style-type: none"> • -40 °C to +125 °C

EMC

Emissions	<ul style="list-style-type: none"> • EN55022, Class A conducted & radiated with external components, see application note
ESD Immunity	<ul style="list-style-type: none"> • EN61000-4-2, 8 kV air, 6 kV contact, Perf Criteria A
Radiated Immunity	<ul style="list-style-type: none"> • EN61000-4-3 10 V/m, Perf Criteria A
EFT/Burst	<ul style="list-style-type: none"> • EN61000-4-4 level 3, Perf Criteria B*
Surge	<ul style="list-style-type: none"> • EN61000-4-5 level 2, Perf Criteria B*
Conducted Immunity	<ul style="list-style-type: none"> • EN61000-4-6 10 V/rms, Perf Criteria A
Magnetic Field	<ul style="list-style-type: none"> • EN61000-4-8 1 A/m, Perf Criteria A

Safety

Safety Approvals	<ul style="list-style-type: none"> • CE (Meets all applicable directives), UKCA (Meets all applicable legislation)
------------------	---

*External input capacitor required 220 μF/100 V.


Models and Ratings

Input Voltage	Output Voltage	Output Current	Input Current ⁽¹⁾		Maximum Capacitive Load	Efficiency	Model Number
			No Load	Full Load			
9-18 VDC	3.3 VDC	5.500 A	60 mA	1.74 A	10,000 µF	90%	JCK2012S3V3
	5.0 VDC	4.000 A	60 mA	1.87 A	6,800 µF	92%	JCK2012S05
	12.0 VDC	1.670 A	30 mA	1.92 A	1,000 µF	90%	JCK2012S12
	15.0 VDC	1.330 A	30 mA	1.92 A	680 µF	90%	JCK2012S15
	±12.0 VDC	±0.835 A	30 mA	1.94 A	±470 µF	89%	JCK2012D12
	±15.0 VDC	±0.665 A	30 mA	1.94 A	±330 µF	89%	JCK2012D15
18-36 VDC	3.3 VDC	5.500 A	35 mA	0.86 A	10,000 µF	91%	JCK2024S3V3
	5.0 VDC	4.000 A	35 mA	0.93 A	6,800 µF	93%	JCK2024S05
	12.0 VDC	1.670 A	25 mA	0.95 A	1,000 µF	91%	JCK2024S12
	15.0 VDC	1.330 A	25 mA	0.95 A	680 µF	91%	JCK2024S15
	±12.0 VDC	±0.835 A	30 mA	0.96 A	±470 µF	90%	JCK2024D12
	±15.0 VDC	±0.665 A	30 mA	0.96 A	±330 µF	90%	JCK2024D15
36-75 VDC	3.3 VDC	5.500 A	25 mA	0.43 A	10,000 µF	91%	JCK2048S3V3
	5.0 VDC	4.000 A	25 mA	0.46 A	6,800 µF	93%	JCK2048S05
	12.0 VDC	1.670 A	15 mA	0.47 A	1,000 µF	91%	JCK2048S12
	15.0 VDC	1.330 A	15 mA	0.47 A	680 µF	91%	JCK2048S15
	±12.0 VDC	±0.835 A	20 mA	0.48 A	±470 µF	90%	JCK2048D12
	±15.0 VDC	±0.665 A	20 mA	0.48 A	±330 µF	89%	JCK2048D15

Notes

- Input current specified at nominal 12, 24 V or 48 V input.
- Cross regulation is ±5% when one output is at 100% and the other is varied between 25% and 100%.
- Measured with 20 MHz bandwidth and 1 µF ceramic capacitor across output rails.
- For heatsink option add '-HK' to the end of the part number.

Mechanical Details




PIN CONNECTIONS		
Pin	Single	Dual
1	+Vin	+Vin
2	-Vin	-Vin
3	+Vout	+Vout
4	Trim	Com
5	-Vout	-Vout
6	Remote On/Off	Remote On/Off

Notes


- All dimensions are in inches (mm).
- Weight: 0.07 lbs (30 g)
- Pin diameter: 0.04 ±0.002 (1.0 ±0.05)
- Pin pitch tolerance: ±0.014 (±0.35)
- Case tolerance: ±0.02 (±0.5)

Application Notes

Derating Curve




External Output Trim



- For 3.3 V output:**
Trim +10%, R = 10 k typical
Trim - 10%, R = 15 k typical
- For 5 V output:**
Trim +10%, R = 10 k typical
Trim - 10%, R = 5 k typical
- For 12 V output:**
Trim +10%, R = 22 k typical
Trim - 10%, R = 5 k typical
- For 15 V output:**
Trim +10%, R = 20 k typical
Trim - 10%, R = 5 k typical

Input Filter



Remote On/Off Control

- Output On >3.0 VDC or open circuit
Output Off <1.2 VDC or short circuit pins 2 & 6