


PNP General Purpose Transistor

FEATURES

- Epitaxial planar die construction.
- Complementary NPN type available (MMBT4401).
- Also available in lead free version.
- Ideal for medium power amplification and switching.

APPLICATIONS

- Ideal for medium power amplification and switching











MAXIMUM RATING @ Ta=25°C unless otherwise specified

Symbol	Parameter	Value	UNIT
V _{CBO}	collector-base voltage	-40	V
V _{CEO}	collector-emitter voltage	-40	V
V _{EBO}	emitter-base voltage	-5	V
I _C	collector current (DC)	-0.6	A
P _C	Collector dissipation	0.35	W
T _J , T _{stg}	junction and storage temperature	-55-150	°C

ELECTRICAL CHARACTERISTICS @ Ta=25°C unless otherwise specified

Symbol	Parameter	Test conditions	MIN.	MAX.	UNIT
$V_{(BR)CBO}$	Collector-base breakdown voltage	$I_C = -100\mu A, I_E = 0$	-40		
$V_{(BR)CEO}$	Collector-emitter breakdown voltage	$I_C = -1mA, I_B = 0$	-40		
$V_{(BR)EBO}$	Emitter-base breakdown voltage	$I_E = -100\mu A, I_C = 0$	-5		
I_{CBO}	collector cut-off current	$I_E = 0; V_{CB} = -35V$	-	-0.1	μA
I_{CEO}	collector cut-off current	$I_E = 0; V_{CB} = -35V$		-0.1	μA
I_{EBO}	emitter cut-off current	$I_C = 0; V_{EB} = -4V$	-	-0.1	μA
h_{FE}	DC current gain	$V_{CE} = -1V; I_C = -0.1mA$ $V_{CE} = -1V; I_C = -1mA$ $V_{CE} = -1V; I_C = -10mA$ $V_{CE} = -2V; I_C = -150mA$ $V_{CE} = -2V; I_C = -500mA$	30 60 100 100 20	300	
$V_{CE(sat)}$	collector-emitter saturation voltage	$I_C = -150mA, I_B = -15mA$ $I_C = -500mA, I_B = -50mA$	-	-0.4 -0.75	V
$V_{BE(sat)}$	base-emitter saturation voltage	$I_C = -150mA; I_B = -15mA$ $I_C = -500mA; I_B = -50mA$	-0.75	-0.95 -1.3	V
f_T	transition frequency	$I_C = -20mA; V_{CE} = -10V;$ $f = 100MHz$	200	-	MHz

TYPICAL CHARACTERISTICS @ $T_a = 25^\circ C$ unless otherwise specified




Dimensions in inch (mm)

SOT-23

