

REVISIONS							
REV	ECO	DESCRIPTION	DATE	BY	APPR		
A1	-	RELEASE NEW DRAWING	01/MAR/22	IAN	TOMMY		





MATERIAL:

HOUSING: THERMOPLASTIC; BLACK

SEAL: SILICONE RUBBER

2. MODIFICATIONS: BACKSHELL RING ADAPTER (BRA);

REDUCED DIA. WIRE SEAL;

- 3. SPECIFICATIONS:
  - 3.1 OPERATING TEMPERATURE: -55°C TO +125°C.
  - 3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
    3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.

  - 3.4 MOISTURE RESISTANCE:

IP68(IM OF WATER FOR A PERIOD OF 24 HOURS, MATED


CONDITION);

IP69K(MATED CONDITION)

- 3.5 MATING CYCLE DURABILITY: 100 CYCLES
- 3.6 RoHS COMPLIANT
- 4. MATING PART: AHDP02-24-35S\* & AHDP04-24-35S\* ( \* = SEAL TYPE )
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

## 6 CONTACT SIZE AND WIRE RANGE:

CONTACT SIZE	MIN. INSUL O.D.	MAX. INSUL O.D.	TYPICAL WIRE RANGE	CURRENT RATING
20	1.02 mm (.040 in)	2.41 mm (.095 in)	16-22 AWG (1.5-0.35mm²)	7.5 AMPS
16	1.35 mm (.053in)	3.05 mm (.120 in)	14-20 AWG (2.0-0.5mm²)	13 AMPS



BACKSHELL RING ADAPTER -BLUE

	AHDP06-2	4-35PR-BRA				REF:H	DP26-24-35PE-L017		
QUANTITY	PART N	IUMBER				DE	SCRIPTION		ITEN
		MA	TE	RIA	<b>NLS</b>	3 LI:	ST		
UNLESS OTHERWISE SPECIFIED		SIGNATUR	ES C	DATE	1 Amphanal		I		
All dimensions a     Tolerances are a     PL DEC ±0.30	as follows:	DRAWN: IAN.XIAO	01	/MAR/22	Amphenol				
2 PL DEC ±0.15 3 PL DEC ±0.08	Fractions ±1/64 Angles ±1°	CHECKED: SULLEN.ZHA	NG 02	/MAR/22		Sin	e Systems - www.ampher	nol-sine.com	
3) Note reference	- /x	ENGINEER:			44724 Morley Drive				
MATERIAL SPECIFICATIONS:		APPROVAL: TOMMY.X	E 03	3/MAR/22			Clinton Township, MI 480	)36	
		CUSTOMER:					35POS,PLUG,PIN,	24SZ,	
WEIGH	T: 60.5g	THIS BIGAWING IS SOLT ELED FOR		SEAL,BRA,DURAM	ATE AHDI	)			
PROCESS SPECIFICATIONS:  NEXT ASSY:		INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAI		B	C-	AHDP06-24-3	5PR-BR/	A A1	
		MANUFACTURING VARIA			SCALE: N	ONE	DURAMATE	SHEET 1	or <b>1</b>