GPS Active Antenna Module - Adhesive Mount

APAMP-111

MSL level: Not Applicable

FEATURES:

- High Reliability/Sensitivity
- Compact Size
- Easy to install (adhesive tape base)
- SGS
- ROHS Compliant

STANDARD SPECIFICATIONS:


Antenna

Parameters	Min.	Тур.	Max.	Units	Note
Center Frequency		1575.42 ± 1.023		MHz	
Bandwidth	10.0			MHz	
VSWR at Center Frequency			1.5:1		
Polarization Model		RHCP			(Right Hand Circular Polarization)
Impedance		50		Ω	
Gain		4.5		dBic	(Based on 70× 70mm ground plane)
Operating Temperature	-40		+80	°C	
Storage Temperature	-45		+85	°C	

Low Noise Amplifier (LNA)

Parameters	Min.	Тур.	Max.	Units	Note
Center Frequency		1575.42 ± 1.023		MHz	
DC Voltage	3.0		5.0	V	
Gain	25	28	31	dB	$(+25^{\circ}C \pm 10^{\circ}C)$
Output VSWR			2.0		
Noise Figure			1.5		$(+25^{\circ}C \pm 10^{\circ}C)$
DC current	5.5	8.5	11.5	mA	(At 3.0V)

> ANTENNA'S IMPEDANCE AND RETURN-LOSS CHARACTERISTICS



Test condition: 25x25mm ground



5101 Hidden Creek Lane Spicewood Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sale please visit: www.abracon.com REVISED:



06.29.2021

RoHS/RoHS II compliant Lead in copper alloy exemption (6c); and Lead in glass exemption (7c-I)

38.3 X 35 X 13.5mm

TYPICAL APPLICATIONS:

- Automotive Navigation
- Automotive Monitoring
- Personal Tracking


GPS Active Antenna Module - Adhesive Mount

APAMP-111


RoHS/RoHS II compliant Lead in copper alloy exemption (6c); and Lead in glass exemption (7c-I)



LNA REFLECTION PROFILE



OUTLINE DRAWING:



Parameters	Description
L (Cable Length)	300±10cm
Antenna	Dielectric Ceramic
RF Cable	RG174
PCB	FR4
RF Connector	SMA-J3
Shielding	Tinplate
Thickness	13.5mm
Adhesive Tape	3M9448A

Unit:mm



5101 Hidden Creek Lane Spicewood Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sale please visit: www.abracon.com

06.29.2021 **REVISED:**

> ABRACON IS ISO9001-2015 CERTIFIED

GPS Active Antenna Module - Adhesive Mount



APAMP-111

RoHS/RoHS II compliant Lead in copper alloy exemption (6c); and Lead in glass exemption (7c-I)

Environmental Specification

Parameters	Specification		
Operating Temperature	-40°C to +80°C		
Storage Temperature	-40°C to +85°C		
RoHS/ RoHS II Compliant	Yes		
Material Composition	Lead in copper alloy exemption (6c); and Lead in glass exemption (7c-I)		
IP Rating	IP66		
ESD Protection	±6 kV (direct discharge)		
	±8 kV (air discharge)		
Mounting Type	Adhesive Tape		
MSL Level	N/A		
Handling	No special handling conditions		

PRODUCT IMAGE:



PACKAGING:

Each 630 x 460 x 105 mm size carton includes 100 pcs antenna, each lattice contains 2 antennas.





CAUTION:

- (1) Do not apply excess mechanical stress to the component body or terminations. Do not attempt to re-form or bend the components as this will cause damage to the component.
- (2) Do not expose the component to open flame.
- (3) This specification applies to the functionality of the component as a single unit. Please insure the component is thoroughly evaluated in the application circuit.

ATTENTION: Abracon LLC products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



5101 Hidden Creek Lane Spicewood Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sale please visit: www.abracon.com REVISED: 06.29.2021

ABRACON IS ISO9001-2015 CERTIFIED