



ANATECH ELECTRONICS INC
RF & Microwave Filters & Products

70.0 MHz Saw Filter

Part Number: AM70S211



Parameters Description	Unit	Minimum	Typical	Maximum
Center Frequency (Fo)	MHz	69.92	70.0	70.08
Insertion Loss at Fo	dB	-	21.0	22.5
Passband Ripple Variation	dB	-	0.55	1.00
Group Delay Variation	nsec	-	150	200
Absolute Delay at Fo	µsec	-	2.59	-
Bandwidth at 3.0 dB	MHz	1.50	1.68	-
Bandwidth at 40.0 dB	MHz	-	2.70	3.00
Ultimate Rejection	dB	50	55	-
Substrate Material	112-LiTaO ₃			

Parameters Description	Unit	Minimum	Typical	Maximum
Operation Temperature Range	°C	-30	-	+80
Storage Temperature Range	°C	-40	-	+85
Maximum DC Voltage	V	-	-	10
Maximum Input Power	dBm	-	-	10
Source Impedance (Single Ended) ₁	Ω	-	50	-
Load Impedance (Single Ended) ₁	Ω	-	50	-
Package Size	20.1 x 12.5 x 5.0 mm			




70.0 MHz Saw Filter


Part Number: AM70S211



Outline Drawing:



Matching Configuration:



Bottom View

Source / Load Impedance = 50Ω

Ambient Temperature = 25°C



70.0 MHz Saw Filter

Part Number: AM70S211



Frequency Response:

