BWCC Series For USB 2.0, IEEE1394b, LVDS



A full series of common mode choke is designed for excellent noise attenuation with compact sizing for use in wide range of applications. Both standard series and custom designs are available.

• USB line for personal computers and peripheral


• LVDS, panel line for liquid display panels, graph card etc

Applications

Features


- RoHS Compliant
- Miniature SMD type common mode filter for fully automated assembly
 IEEE 1394 line for personal computers, DVC, STB
- Excellent solderability

Product Identification




Shape and Dimensions

BWCC00201208



Recommended Pattern



D	imensions in mm									
	TYPE	Α	в	С	D	Е	F	G	н	I
	BWCC00201208	2.0±0.2	1.2±0.2	0.8±0.1	0.5	0.4	0.5	1.27	0.8	2.6



Electrical Characteristics

Part Number	Impedance (Ω)	Tolerance (±%)	Test Frequency (MHz)	RDC (Ω) Max	IDC (mA)	Rated Voltage (Vdc)	Withstanding Voltage (Vdc)	Insulation Resistance (MΩ) Min
BWCC00201208300_02	30	20	100	0.20	1300	50	125	10
BWCC00201208420_02	42	20	100	0.20	1300	50	125	10
BWCC00201208670_02	67	20	100	0.25	1200	50	125	10
BWCC00201208900 02	90	20	100	0.27	1000	50	125	10
BWCC00201208121_02	120	20	100	0.30	900	50	125	10
BWCC00201208181 02	180	20	100	0.40	700	50	125	10
BWCC00201208261 02	260	20	100	0.60	700	50	125	10

Note: When ordering, please specify tolerance code. Tolerance: M= $\pm 20\%$

• Operating temperature range - 40°C ~ 105°C(Including self - temperature rise)

- RDC : SINGLE WIRE TEST VALUE
- IDC for Inductance drop 10% from its value without current.
- Measure Equipment :
 - Z : Agilent HP4291A


RDC : HP4338B or Chroma 16502 (Single Wire Test Value)

IDC : HP4284A+HP42841A/HP4285A+HP42841A

Insulation Resistance : Agilent HP4339B

Test Instruments: HP4291A Material/Impedance Analyzer


Typical Impedance vs. Frequency



Please be sure to request approval specifications that provide further details of the products. Kindly note that the content of these specifications are subject to change or may be discontinued without prior notice. This product may not be designed/used in medical or high risk applications without Chilisin approval. Please contact our sales department before ordering.




Packaging Specifications





Reel Dimensions



Dimensions in mm

	ТҮРЕ		Tape Dimensions							Reel Dim	Quantity		
		A	в	т	w	Ρ	F	к	A	В	С	D	PCS / Reel
-	BWCC00201208	1.46	2.3	0.23	8	4	3.5	1.1	178	60	12	1.5	2000

